


**LOW LEAD COMPLIANT
 2 PC 600 WOG BALL VALVE**

Features:


- 600 WOG
- 150 WSP
- Full Port
- NSF 61 Annex G Certified (UL) (Annex G references NSF 372)
- Meets MSS SP-110 Standards
- Blow-out Proof Stem
- Adjustable Packing
- Threaded NPT Ends Per ANSI B 1.20.1
- 100% Electronically Tested in Open and Closed Position at 80 PSI
- Optional Lock Lever *
- Optional Stem Extension
- Optional Tee Handle (to 1")
- Optional Oval Handle
- Optional Memory Stop



NOT FOR USE AT OR BELOW GROUND LEVEL



OPTIONS



Lock Lever



Stem Extension



Tee or Oval Handle



Memory Stop

Low Lead Compliant: Referring to laws defining "Lead Free" as wetted surface of pipe, fittings and fixtures in potable water systems that have a weighted average lead content $\leq 0.25\%$ per the Safe Drinking Water Act (Sec. 1417) amended 1-4-2011 as well as other state regulations.



Figure Number Matrix

FNW X420A Size			
SIZE CODE			
1/4 = B	3/4 = F	1-1/2 = J	3 = M
3/8 = C	1 = G	2 = K	4 = P
1/2 = D	1-1/4 = H	2-1/2 = L	



Gas Approvals

- CSA Class 3371-10, CGA 3.16, 125 PSIG, -40°F~149°F (1/4"~2")
- CSA Class 3371-88, ANSI Z21.15/CSA9.1, 1/2 PSIG, 32°F~188.6°F (1/2"~2")
- CSA Class 3371-90, ASME B16.33/b16.38, 125 PSIG, -40°F~149°F (1/4"~2")
- CSA Class 3371-92, ASME B16.44, 5 PSIG, -40°F~149°F (1/2"~2")
- CSA Class 3371-94, ASME B16.33, 125 PSIG, -40°F~149°F (1/2"~2")
- CSA Class 3371-97, UL-125, 250 PSIG, -40°F~130°F (1/4"~3/8")
- UL Class YRPV, ANSI/UL-842, 250 PSIG, -20°F~125°F (1/4"~2")
- UL Class YSDT, ANSI/UL-125, 250 PSIG, -40°F~130°F (1/4"~2")

Kit Codes (Order Separately)

FNW X420A Kit Size	
KIT TYPE	SIZE CODE
Locking Handle = LHK	1/4"~1/2" = BD
Stem Extension = SE	3/4"~1" = FG
Tee Handle = THK	1-1/4"~1-1/2" = HJ
Oval Handle = OHK	2" = K
Memory Stop = MSK	
Stainless Handle = SSHK	