



Frigidaire 30" Freestanding Electric Range

Model: FFEF3015LS
29-7/8" W x 28-1/2" D x 47" H
MSRP: \$579.00

 Stainless Steel

Specifications

Product Code: FFEF3015LS
Product Type: Ranges
Power Type: Electric
Size: 30"
Installation Type: Free-Standing
Color: Stainless Steel

Certifications & Approvals

Agency Approval: UL

Exterior Specifications

Door Finish: Glass with Overlay
Handle Color: Black

Cooking Controls

Bake: Yes
Broil: Low and High
Preheat: Integrated with Bake
Self-Clean: 2, 3 Hours (Scroll thru)
Interface: Membrane
Oven Light: Oven Light
Lockout: Yes
Timer Lockout: Yes
Main Oven: Self Clean
Timed Shut-off: 12 hours
Timer: Yes
Timed Cook Option: Yes

Cooktop Specifications

Cooking Surface: Upswept Coil
Right Front: 6" - 1,250 Watts
Right Rear: 6" - 1,250 Watts
Left Front: 8" - 2,100 Watts
Left Rear: 8" - 2,100 Watts
Knob Type: Plastic

Oven Specifications

Oven 1 Type: Main

Oven 1 Bake: 2,600 Watts
Oven 1 Baking System: Even Baking Technology
Oven 1 Broil : 3,000 Watts
Oven 1 Broiling System: Vari-Broil™ High/Low
Oven 1 Interior Lighting: 1
Oven 1 Rack Configuration: 2 Standard
Oven 1 Cleaning System: Self-Clean
Oven Window: Extra-Large

Exterior Dimensions

Height: 47"
Width: 29-7/8"
Depth: 28-1/2"
Depth (to Center of Arc): 28-1/2"
Depth (with Door 90° Open): 48-3/8"

Electrical Specifications

Power Supply Connection Location: Rear Centerline
Lower
Voltage Rating: 240V / 208V, 60Hz
Connected Load (kW Rating) @ 120V: 12.5 / 9.5

General Specifications

Product Weight (lbs): 115
Shipping Weight (lbs): 138
