


CABLE TIES

Product Features

- Available in 7-1/2" to 48"
- · High tensile strength
- Manufactured from type 6/6 nylon
- UL181B approved on 36" and 48" ties
- 7-1/2" 36" black are UV rated under standard 62275

Warranty

1-year limited warranty







This is for 1565 only 7-1/2" – 14"



This is for 181 and 1565 24" - 48"

Specifications

PSCTBV	Dim.	Inches	7-1/2"— 50lb	
PSCTBV1000	Α	0.180		
1 001 000	В	0.054		
	С	7.563	Job No.	B7S
	D	0.310	Drawing No.	
	E	0.202	Material	Nylon 6/6
	F	0.300	Designed	

DOCTRA	Dim.	Inches	11"— 50lb	
PSCTB11	Α	0.180		
	В	0.054		
	С	11.125	Job No.	B11S
	D	0.310	Drawing No.	
	E	0.202	Material	Nylon 6/6
	F	0.300	Designed	

PSCTB14	Dim.	Inches	44.4/011	FAII
	Α	0.180	14-1/2"— 50lb	
	В	0.054		
	С	14.563	Job No.	B14S
	D	0.310	Drawing No.	
	E	0.202	Material	Nylon 6/6
	F	0.300	Designed	

DOOTDNIG 4	Dim.	Inches	24" — 175lb	
PSCTBN24	Α	0.350		
	В	0.054		
	С	24.25	Job No.	B24H
	D	0.540	Drawing No.	
	E	0.382	Material	Nylon 6/6
	F	0.505	Designed	

PSCTN36	Dim.	Inches	36" — 175lb	
PSCTB36	Α	0.350		
1 001 000	В	0.087		
	С	36.500	Job No.	B36H
	D	0.540	Drawing No.	
	Е	0.382	Material	Nylon 6/6
	F	0.505	Designed	

PSCTN48	Dim.	Inches	4011	47511	
PSCTB48	Α	0.355	48" — 175lb		
1 001040	В	0.072			
	С	47.938	Job No.	B48H	
	D	0.552	Drawing No.		
	E	0.369	Material	Nylon 6/6	
	F	0.520	Designed		