

# Dayton® Undermount Single Bowl Sink

#### **GENERAL**

Sink is formed of #18 (1.2mm) gauge, 300 series nickel bearing stainless steel. Undermount.

#### **DESIGN FEATURES**

Bowl Depth: 8" (203mm).

Finish: Exposed surfaces are polished to a Radiant Satin finish. Underside: Sound dampening pad with spray undercoating to dampen sound and reduce condensation.

#### **OTHER**

Drain Opening: 3-1/2" (89mm).

NOTE: All Dayton undermount sinks are designed to affix easily to the underside of any solid surface countertop.

Sink complies with ASME A112.19.3/ CSA B45.4



Sinks are listed by IAPMO® as meeting the applicable requirements of the Uniform Plumbing Code®, International Plumbing Code®, and National Plumbing Code of Canada.

#### **OPTIONAL ACCESSORIES**

Bottom Gird: GBG1318SS

Cutting Board: CBR1316 (sink must be installed with a 1/2" reveal

for cutting board to fit properly)

Drain: D1125


Rinsing Basket: LKWRB1318SS, LKWERBSS

Utensil Caddy: LKWUCSS Mounting Clip: LKUCLIP8 Template: 74180747


#### **SINK DIMENSIONS (INCHES)\***

Model	Overall		Inside Bowl			Minimum Cabinet
Number	L	W	L	W	D	Size
DXUH1318	16	201/2	131/2	18	8	24
	(406mm)	(520mm)	(343mm)	(45/mm)	(203mm)	(610mm)

<sup>\*</sup>Length is left to right. Width is front to back.




# Model DXUH1318




Model DXUH1318



## **Electronic Dual Template Mounting Option** (Download DXF File from www.elkaypro.com)



### 1/8" Overhang



In keeping with our policy of continuing product improvement. Elkay reserves the right to change product specifications without notice. Please visit elkayusa.com for most current version of Elkay product specification sheets.

This specification describes an Elkay product with design, quality and functional benefits to the user. When making a comparison of other producers' offerings, be certain these features are not overlooked.

2 1/4" R (56mm)