

MJ TRANSITION ACCESSORY PACK WITH GLAND

Product Features

Rubber Gasket

- Material SBR
- Standard ANSI / AWWA C111 / A21.11
- ASTM Test Methods
 - Hardness D2240-91
 - Tensile Strength & Elongation D412-92
 - Minimum Aging D572-88
 - Maximum Compression D395-89
 - NSF/ANSI Standard 61 Compliant

Ductile Iron Gland

- Material ASTM A536, Grade 65-45-12
- Standard ANSI / AWWA C153 / A21.53
- Coating Asphaltic seal coat inside and out in accordance with ANSI / AWWA C104 / A24.1

Low Alloy Steel T-Head Bolts & Nuts

• Material & Dimension - ANSI / AWWA C111 / A21.11

Ductile Iron Gland Low Alloy Steel T-Head Bolt & Nut



Product Specifications

Includes Gland, Transition Gasket and standard T-Head Bolts

PART#	SIZE
IMJTGAPK	2"
IMJTGAPM	3"
IMJTGAPP	4"
IMJTGAPU	6"
IMJTGAPX	8"
IMJTGAP10	10"
IMJTGAP12	12"
· ·	

PROSELECT Glands, Gaskets, T-head Bolts and Mechanical Joint Accessory Packs are sold exclusively through Ferguson Enterprises and its affiliates.

Ferguson Enterprises guarantees the quality and compliance to the listed specifications.

PROSELECT is a registered trademark of Ferguson Enterprises.

Warranty and Codes

This PROSELECT product carries a 1-year limited warranty.