The Com-Pak Bath

The premier choice for today's bathrooms





General Information:

The Com-Pak Bath Heater is our most versatile and stylish heater. Equipped with a built-in thermostat and 60-minute timer, it is a great option for adding supplemental heat to any room. The 60-minute auto-timer overrides the thermostat setting for instant warmth and comfort.* The Com-Pak Bath Heater is Cadet's first heater with both multi-volt and multi-watt options available. Because the Com-Pak Bath Heater fits into any C-series wall can, it is a great option for replacement, remodel or new construction.

*Once timer expires; control of the heater will return to the thermostat and the previous set-point setting.





S

SAFETY

Thermal Safeguard

 High temperature manual reset: turns off heater if normal operating temperatures are exceeded



QUALITY

- Durable steel tube and plate constructed heating element - painted to resist rusting
- Powder coat paint process eliminates sharp metal edges



COMFORT

- Ideal for instant warmth in bathrooms
- Advanced built-in controls
- Thermostat: range 45°F-85°F: with disabled (no heat) position
- 60 minute timer overrides thermostat for instant warmth



CONVENIENCE

- Multi-Volt and Multi-Watt options
- Unique low profile grill only 1/2" deep

Architectural Information:

Fan forced electric air heaters shall be UL listed, factory rated 120V/240V or dual field rated 208V/240V. The painted wall mounting can is made from 20-gauge sheet metal with six electrical knockouts and a 22 cubic inch wiring compartment. Each heating unit shall be of unitized construction and attach to the wall can with a single screw and shall be self contained and completely separate from the wall mounting can. Elements shall be tube and plate, painted, with an over-sized 16 amp rating at 240V high temperature manual reset limit switch. A centrifugal blower shall be driven by an impedance protected motor. The motor shall be totally isolated from the heating element. Metal grill shall be of one piece, 20-gauge construction, and finished with a powder coat paint system.

Carton Details

Heater Assembly Only Carton

DIMENSIONS | 11.25"W x 8.5"H x 5.25"D

PALLET QTY. | 80 **CUBE** | .30

Complete Unit Carton

DIMENSIONS | 14.5"W x 10.5"H x 5.75"D

PALLET QTY. | 88 **CUBE** | .51



Heater Assembly with Thermostat and Timer



Wall Can

The Com-Pak Bath



Technical Information:

All heaters include a built-in single pole thermostat and 60-minute timer. The Com-Pak Bath Heater is not to be used with a wall thermostat. The multi-volt option must be configured for the correct voltage before installing the heater. The multi-watt option must be configured for the desired wattage before installing the heater. UL requires heater to be placed a minimum distance of 6" from adjacent surfaces and 4.5" from the floor. Manufacturer recommends installation 12" from all surfaces. A 3' minimum clearance is required for furniture or other objects placed directly in front of heater.

NOTE: Manufacturer recommends installing heater assembly after walls are finished. Heater must be cleaned every six months minimum.

Ordering Information:

Recommended for elevations under 10,000 feet. Available in white only.


UP	C Code –	-		WATTS—			AMPS——				
	Part#	Model#	Description	240V	208V	120V	240V	208V	120V	Wt./Lbs	
027418	65101 3	CBC103TW	Complete Unit, Multi-Volt, White	1000		1000	4.16		8.33	8	
027418	65103 7	CB103T	Heater Assembly, Stat & Timer, Multi-Volt	1000		1000	4.16		8.33	4.7	
027418	65104 4	CB132T	Heater Assembly, Stat & Timer, Multi-Watt	500/800/1300	375/600/975		2.09/3.33/5.42	1.80/2.89/4.69		4.7	
027418	65105 1	CBC132TW	Complete Unit, Multi-Watt, White	500/800/1300	375/600/975		2.09/3.33/5.42	1.80/2.89/4.69		8	


— UPC Code —


ACCESSORIES

	Part#		Model#	Description	Wt./Lbs	
027418	65110	5	CBGW	Grill, White w/ Parts	1.5	
027418	65150	1	CBGW5	Grill, Five Pack w/ Parts	7	
027418	67060	1	CC10	CS Wall Can Ten Pack	22.5	
027418	67061	8	CC	CS Wall Can Single Pack	2.5	
027418	67100	4	CAMA	18.5" x 22" Metal Adapter Plate CS Series, Almond	3.5	
027418	67105	9	CAMW	18.5" x 22" Metal Adapter Plate CS Series, White	3.5	
027418	67110	3	SAMA	12" x 21.25" Metal Adapter Plate CS Series, Almond	2	
027418	67115	8	SAMW	12" x 21.25" Metal Adapter Plate CS Series, White	2	

Thermostat temperature range 45°F to 85°F







Wall Can Dimensions:

71/4"W x 111/2"H x 4"D

