
The Register Plus

The premier choice for all rooms







SAFETY

High temperature manual reset: turns off heater if normal operating temperatures are exceeded



QUALITY

Powder coat paint process eliminates sharp metal edges



EASY

Wall can designed for quick installation with mounting legs that minimize measuring time



COMFORT

Commercial grade steel element is quiet and efficient

General Information:

The Register Plus is Cadet's premier fan forced heater line and is often chosen for its similar appearance to central system register vents. Models are offered with both fixed and multi-watt capabilities (multi-watt models factory preset at their maximum wattage). A large squirrel cage blower quietly provides increased airflow allowing for lower surface and air-at-surface temperatures. Cadet recommends a wall-mounted thermostat for optimum performance, or you may prefer the convenience of an optional field mount thermostat kit.



Fan forced electric air heaters shall be UL listed, factory rated at 120V, 208V, or dual field rated 208V/240V. A 20 gauge wall mounting can with four knockouts shall be provided with each complete heater. The element and blower shall be of unitized construction and shall attach to wall can with a single screw. Elements shall be steel-finned type, with an oversized 25 amp rating at 240V high temperature manual reset limit switch. A tangential cylindrical blower delivering approximately 50 to 60 CFM shall be driven by an impedance protected motor with permanently lubricated, vibration isolated, dust sealed bearings. Metal grill shall be of one piece construction and finished with a powder coat paint system.





Carton Details

Heater Assembly Only Carton

DIMENSIONS | 12"W x 7.5"H x 5.25"D

PALLET QTY. | 100 CUBE | .27

Complete Unit Carton

DIMENSIONS | 14.375"W x 9.375"H x 5.75"D

PALLET QTY. | 96 CUBE | .45





Wall Can



Technical Information:

A thermostat is required. For optimum comfort use a Cadet electronic thermostat. Fan heaters and thermostats work best when installed on an inside wall. A double pole, built-in thermostat may be installed in the field. UL requires heater to be placed a minimum distance of 6" from adjacent surfaces and 4.5" from the floor. Manufacturer recommends installation of 12" from all surfaces. A 3' minimum clearance is required for furniture or other objects placed directly in front of heater.

NOTE: Manufacturer recommends installing heater assembly after walls are finished. Heater must be cleaned every six months minimum.

Ordering Information:

Recommended for elevations under 7500 feet. Complete unit available in white only.

UPC	Code —				—watts—			—— AMPS —		
	Part#	Model#	Description	240V	208V	120V	240V	208V	120V	Wt./Lbs
027418	63313 2	RMC202W	Complete Unit, White	2000	1500		8.33	7.21		9
027418	63314 9	RMC162W	Complete Unit, White	700/900/1600	525/675/1200		2.92/3.75/6.67	2.52/3.25/5.77		9
027418	63315 6	RMC151W	Complete Unit, White			500/1000/1500			4.17/8.33/12.50	9
027418	63316 3	RMC208W	Complete Unit, White		2000			9.62		9
027418	00322 5	RM222	Heater Assembly Only	2250	1687		9.37	8.11		4.5
027418	00306 5	RM202	Heater Assembly Only	2000	1500		8.33	7.21		4.5
027418	00307 2	RM162	Heater Assembly Only	700/900/1600	525/675/1200		2.92/3.75/6.67	2.52/3.25/5.77		4.5
027418	00311 9	RM102	Heater Assembly Only	1000	750		4.17	3.61		4.5
027418	00308 9	RM151	Heater Assembly Only			500/1000/1500			4.17/8.33/12.50	4.5
027418	00309 6	RM208	Heater Assembly Only		2000			9.62		4.5
027418	00313 3	RM168	Heater Assembly Only		700/900/1600			3.36/4.33/7.69		4.7
027418	00310 2	RM108	Heater Assembly Only		1000			4.81		4.5
027418	00323 2	RM158	Heater Assembly Only		1500			7.21		4.5

- UPC Code -				ACCESSORIES	
	Part	#	Model#	Description	Wt./Lbs
027418	00275	4	RMGW	RM Grill w/ Parts, White	1.5
027418	00276	1	RMGA	RM Grill w/ Parts, Almond	1.5
027418	63113	8	RMGW5	RM Grill Five Pack w/ Parts, White	7.5
027418	63114	5	RMGA5	RM Grill Five Pack w/ Parts, Almond	7.5
027418	63115	2	RMC	RM Wall Can Single Pack	3.25
027418	63116	9	RMC5	RM Wall Can Five Pack	14.25
027418	63123	7	RMT2W*	Double Pole Field Mount Thermostat, White	.44
027418	63124	4	RMT2A*	Double Pole Field Mount Thermostat, Almond	.44
027418	63118	3	RMS4W	Register Surface Mount Adapter, White	5.75

^{*}Thermostat kit temperature range 40°F to 85°F

HDC C-4-

