

## PRODUCT SPECIFICATIONS



### 7016BFD

Contractor+ Front ID Standard Non-belted Full Body Harness

[CONTACT SALES](#)

[COMPARE SRLs](#)

#### Features :

- Proprietary dorsal attachment sleeve supports effortless addition of personal SRLs
- Plated alloy steel low-profile spring tension roller torso adjusters provide simple adjustment
- Breathable padded air-mesh shoulder yoke delivers added user comfort
- Paired lanyard parking keepers provide balanced function for single and twin-leg personal SRLs
- Plated alloy steel dorsal and sternal D-rings with mating buckle chest and tongue buckle leg closures
- Features tongue buckle leg connections with 7 grommeted leg adjustment positions for a wide range of fit
- Complies with ANSI Z359.11-2014



#### Material Specifications

<b>Webbing</b>	Polyester; 5,000 lb min. static strength
<b>D-rings</b>	Plated alloy steel; 5,000 lb min. static strength
<b>Buckles and Adjusters</b>	Plated alloy steel; 3,372 lb min. static strength

#### Performance Specifications

<b>Static Strength</b>	3,600 lb min.
<b>ANSI User Capacity</b>	130 to 310 lb max.
<b>OSHA User Capacity</b>	130 to 425 lb max.

#### Compliant With:

<b>ANSI</b>	Z359.11-2014
<b>OSHA</b>	1926.502 and 1910.140
<b>CSA</b>	Z259.10-2018

**Sizes & Part Numbers**

7016BFDXS - XS	7016BFDS - Small	7016BFDM - Medium	7016BFDL - Large	7016BFDXL - XL	7016BFD2X - 2X	7016BFD3X - 3X	
----------------	------------------	-------------------	------------------	----------------	----------------	----------------	--

---