


Location:




# SYMMONS® Symmetrix®

## Lavatory Faucet S-250 Series Specification Submittal



S-250  
Standard handle

### Feature Highlights

- Cast brass 4 inch (102mm) centerset lavatory faucet
- Quarter turn ceramic control components with two blade handles
- 1/2 inch IPS shanks
- Solid brass construction
- Polished chrome finish (standard)
- Aerator with 2.2 gpm flow rate (8.3 L/min)  
*Optional aerator available in lower flow rates* 

### Standards / Certifications

ASME A112.18.1-2005/CSA B125.1-05

ADA compliant lever handles





WaterSense Certified



### Warranty

- Limited Lifetime - to the original end purchaser in residential / consumer installations
- 5 years - for commercial installations

### S-250 series handle options

Standard	LWG		
 	 		

### Model Numbers

Append appropriate -suffix to model number.

- S-250 Faucet only with lift rod hole
- S-250-0 Faucet only without lift rod hole
- S-250-1 Faucet with lift rod
- S-250-2 Faucet with pop-up drain & lift rod
- S-250-2-G Faucet with grid strainer drain assembly

### Finish Options / Modifications

Append appropriate -suffix to model number.

- Polished chrome (standard)




### Handle Options / Modifications

Append appropriate -suffix to model number.

- LWG Wrist blade handles

### Other Options / Modifications

Append appropriate -suffix to model number.

- OFG Offset grid strainer (model S-250-2-G only)
-  -0.5 Aerator flow restrictor, 0.5 gpm (1.9 L/min)
-  -1.0 Aerator flow restrictor, 1.0 gpm (3.8 L/min)
-  -1.5 Aerator flow restrictor, 1.5 gpm (5.7 L/min)
- VP Vandal resistant aerator, 2.2 gpm (8.3 L/min)
- NA Non-aerated laminar flow outlet, flow rate 2.2 gpm (8.3 L/min)