


CADDY® MACROFIX PLUS NI 429

Finish:
Electro-galvanized Zinc



UL® listed for use with CPVC pipe as a hanger and surge restraint

CPVC Non-Insulated Pipe Clamp


Ø 3/8 Threaded Rod Part Number	Ø M10 Threaded Rod Part Number	Ø M12 Threaded Rod Part Number	Nominal Pipe Size Inches	Outside Dia. Of Pipe (Inches) / mm
4290050EG	595052		1/2	(0.84) / 21.3
! 4290075EG	! 595053		3/4	(1.05) / 26.7
! 4290100EG	! 595054		1	(1.32) / 33.4
! 4290125EG	! 595056		1-1/4	(1.67) / 42.2
! 4290150EG	! 595057		1-1/2	(1.90) / 48.3
! 4290200EG	! 595059		2	(2.37) / 60.3
4290250EG	595061	* 596060	2-1/2	(2.87) / 73
4290300EG	595062	* 596062	3	(3.50) / 88.9
* 4290350EG			3-1/2	(4.00) / 101.6
4290400EG	595063	* 596063	4	(4.50) / 114.3
* 4290500EG	* 595066		5	(5.56) / 141.3

! =FM® Approved

* =Not UL Listed

Installation:

- Insert pipe
- Close pipe clamp by pressing the clamp part upward
- Let screw head lock in the tabs
- Use a screwdriver to tighten the two screws
- Tighten pipe clamp until tabs are parallel



Bottom Beam Installation

Top Beam Installation

To comply with UL203 Listing in the top beam installation the hex nut of the pipe hanger must be inserted onto a threaded rod and rest directly on the structural member.

WARNING:

1. ERICO products shall be installed and used only as indicated in ERICO product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative.
2. ERICO products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
3. All instructions must be completely followed to ensure proper and safe installation and performance.
4. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.
5. Products that are manufactured using spring steel components shall be used only in a non-corrosive indoor environment.
6. All pipe supports, hangers, intermediate components and structural attachments must ONLY be used as described herein and are NEVER to be used for any other purpose.

NOTE: All load ratings are for static conditions and do not account for dynamic loading such as wind, water or seismic loads, unless otherwise noted.

The customer is responsible for:

- a. Conformance to all governing codes.
- b. The integrity of structures to which the products are attached, including their capability of safely accepting the loads imposed, as evaluated by a qualified engineer.
- c. Using appropriate industry standard hardware as noted above.

SAFETY INSTRUCTIONS:

All governing codes and regulations and those required by the job site must be observed.
Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.

All rights reserved. CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

FM is a registered certification mark of FM Approvals LLC, LTD
UL is a registered trademark of Underwriters Laboratories, Inc.

TECHNICAL SUPPORT:

www.erico.com

CFS397_H

1 OF 1

© 2009, 2010, 2011 ERICO International Corporation

ERICO®

