



EZ STREET® COLD ASPHALT

Description

EZ Street® Cold Asphalt is a mixture of asphalt, graded aggregates and polymer additives designed for the permanent restoration of asphalt or concrete.

Primary Uses

- Potholes
- Utility Cuts
- Edge of Pavement Repair
- Small Overlays
- Driveways
- Parking Areas
- Walks
- Large Cracks

Advantages

- Permanent repair - Guaranteed
- Ready to use
- No mixing required
- No heat or tack coat required
- Works in water
- Works in all temperatures & conditions
- Easy to use, easy cleanup
- Instantly ready for traffic
- Environmentally Friendly

Packaging

EZ STREET is supplied in:
50lb./22.6kg poly-vinyl bags
2000lb. (909kg) Super Sack

Coverage

50lbs. (22.6kg) covers 3 sq.ft. (.27m²) at 1.5" (38mm) thick.

Typical Properties

TEST	METHOD	SPECIFICATION
Extraction	ASTM D2172	0.5 %
Gradation	AASHTO T-30	Tolerance within EZ STREET Specification
Resistance to Water Damage	AASHTO T-182 modified	+ 95 %
Outdoor Shelf Life	Visual	6 months min., 50 ton min. @ 6' height

Guide to Application

Preparation:

Clean area and remove all loose debris, unsound concrete, blacktop, grease, oil, paint, and any other foreign materials that will inhibit performance.

Mixing:

No mixing necessary. Ready to Use.

Placement:

Place EZ Street in area to be repaired. Compact/tamp with roller, vibratory plate compactor or vehicle to just 25% higher of the repair depth over level of existing pavement. For applications deeper than 4" (102mm), place EZ Street in 2" (50mm) lifts, compacting each layer before applying the next layer.

Curing:

After placement and compaction, EZ Street will cure to a permanent repair in 7 days.

Limitations:

DO NOT add water, petroleum, or any other materials.

Shelf Life

One year from date of manufacture.