


HAMPTON® TWO-HANDLE WIDESPREAD LAVATORY FAUCET WITH BRASS TRADITIONAL SPOUT



GENERAL DESCRIPTION:

Cast brass valve bodies with flexible hose connections for 6" to 12" (152mm to 305mm) installations. 1/4 turn washerless ceramic disc valve cartridges - reversible for use with either lever or cross handles. Cast brass spout. One-half inch male inlet shanks with brass coupling nuts. 20" (500mm) long flexible stainless steel drain cable is pre-assembled to spout. Metal Speed Connect[®] drain body with 1-1/4 inch (32mm) tail piece. 1.5 gpm/5.7L/min. maximum flow rate.

PRODUCT FEATURES:

Brass Construction: Durable. Ideal for prolonged contact with water. Provides the finest surface for application of colors and finishes.

Ceramic Disc Valve Cartridges: Assures a lifetime of drip-free performance.

Lead Free: Faucet contains $\leq 0.25\%$ total lead content by weighted average.

Exclusive Speed Connect Metal Drain:

- Fewer parts. Installs in less time.
- No adjustments required seals the first time, every time.
- Flexible stainless steel cable installs effortlessly in tight spaces.

Exclusive Handle Alignment System: Allows fine tuning of handle position.

Choice of Finishes: Wide range of durable finishes.

SUGGESTED SPECIFICATION:

Two handle widespread lavatory faucet shall feature cast brass valve bodies with flexible hose connections for 6" to 12" installations. Shall also feature 1/4 turn washerless ceramic disc valve cartridges that are reversible for use with cross or lever handles. Shall also feature a metal drain body with stainless steel cable actuation. Fitting shall be American Standard Model # 7871.


American Standard

HAMPTON® TWO-HANDLE WIDESPREAD LAVATORY FAUCET WITH BRASS TRADITIONAL SPOUT

CODES AND STANDARDS

These products meet or exceed the following codes and standards:

ASME A112.18.1 CSA B 125 NSF 61/Section 9 and Annex G



				Finish Options		
	Product			Polished Chrome	PVD Polished Brass	PVD Satin Nickel
	Number	Description		002	099	295
B	7871.712	Hampton Widespread with Metal Speed Connect [®] Pop-up drain. Porcelain Lever handles.	Ŀ		N/A	
B	7871.732	Hampton Widespread with Metal Speed Connect Pop-up drain. Metal Lever handles.	J.			

N/A = NOT AVAILABLE

Meets the American Disabilities Act Guidelines and **ANSI A117.1** Requirements for the physically challenged.

AERATOR MODIFICATIONS***	Parts Suffix**
0.5gpm (1.9Lpm) PCA* Spray	F05
0.5gpm (1.9Lpm) Vandal Resistant PCA Spray	V05
1.0gpm (3.8Lpm) PCA Aerator	F10
1.0gpm (3.8Lpm) Vandal Resistant PCA Aerator	V10
1.5gpm (5.7Lpm) Vandal Resistant PCA Aerator	V15

AVAILABL	AVAILABLE MODIFICATIONS***			
	Less Pop-Up Drain; Less Hole	LDH		
Handles	Indexed Installed(Red & Blue)	RB		

*PCA — Pressure Compensating

**To modify a product, add suffix after the 4th digit (ex. 2064 F05 101.002)

***Modified product models are **NOT** WaterSense certified.