





WALL CONTROLS




- Model 57V (Ivory), 57W (White)
Electronic Variable Speed Control (3 Amp)**
- Rotary dial for variable selection of fan speed and sound level
 - Positive off position
 - Fits single-gang box
 - Built-in radio noise suppressor
 - 120 VAC, 3.0 Amp capacity
 - For use with all Broan fans within Amp rating except ceiling paddle fans
 - Do not use with impedance protected motor




- Model 59V (Ivory), 59W (White)
60-Minute Time Control**
- Operates continuously or for any set period up to 60 minutes
 - Fits single-gang box
 - 120 VAC, 20 Amp or 240 VAC, 10 Amp capacity
 - Also recommended for low voltage (30V Max) applications
 - For use with all Broan fans and heaters within Amp rating




- Model 61V (Ivory), 61W (White)
15-Minute Time Control**
- Operates for any set period up to 15 minutes (no "continuous on" position)
 - Fits single-gang box
 - 120 VAC, 20 Amp or 240 VAC, 10 Amp capacity
 - Also recommended for low voltage (30V Max) applications
 - For use with all Broan fans and heaters within Amp rating




- Model 62V (Ivory), 62W (White)
60-Minute Time Control with Two Rocker Switches**
- Two, independent, 120 VAC, 15 Amp rocker switches (20 Amp Total)
 - Timer operates continuously or for any set period up to 60 minutes
 - Fits two-gang box
 - 120 VAC, 20 Amp or 240 VAC, 10 Amp timer capacity
 - For use with all Broan fans and heaters within Amp rating



- Model 63V (Ivory), 63W (White)
60-Minute Time Control with Rocker Switch**
- One, independent 120VAC, 15 Amp rocker switch
 - Timer has same features as Model 62V/62W
 - For use with all Broan fans and heaters within Amp rating




- Model 64V (Ivory)
Fan/Light Control with Off-Delay**
- Fan and light operate together when control is turned on. Fan continues to operate for a set time period (user adjustable from 5-60 minutes) after light is turned off
 - Center position turns fan and light off immediately
 - Can also be used with a fan only
 - Fits single-gang box
 - 120 VAC, 4 Amp (fan) and 4 Amp (light) capacity
 - For use with all Broan fans and fan/lights within Amp rating. Requires both sides of the electrical line (hot & neutral) in the switchbox



- Model 65V (Ivory), 65W (White)
Three-Function Control with Brass Finish Metal Wall Plate**

- Model 66V (Ivory), 66W (White)
Three-Function Control with Plastic Wall Plate**


- Model 67V (Ivory), 67W (White)
Three-Function Control with Chrome Finish Metal Wall Plate**
- Three, independent, 120 VAC, 15 Amp rocker switches (20 Amp total)
 - Fits single-gang opening
 - For use with all Broan fans and heaters within Amp rating



- Model 68V (Ivory), 68W (White)
Two-Function Control**
- Two, independent, 120 VAC, 15 Amp rocker switches (20 Amp total)
 - Fits single-gang box
 - For use with all Broan fans and heaters within Amp rating

Broan-NuTone LLC, A Nortek Company, Hartford, Wisconsin 53027

REFERENCE	QTY.	REMARKS	Project
			Location
			Architect
			Engineer
			Contractor
			Submitted by Date




**Model 69V (Ivory), 69W (White)
Single-Function Control**

- Fits single-gang box
- 120 VAC, 15 Amp
- For use with all Broan fans within Amp rating




**Model 69VL (Ivory), 69WL (White)
Single-Function Control with Indicator**

- Red light indicates power is on
- Specially designed for use with Broan Solitaire® Ultra Silent™ fans
- Fits single-gang box
- 120 VAC, 20 Amp




**Model 70V (Ivory)
Whole House Ventilator Wall Thermostat**

- Line voltage thermostat automatically activates the ventilator if house temperature rises above the preset comfort setting
- Fits single-gang box
- 120, 250, 277 VAC; 22 Amp capacity
- For use with all Broan whole house ventilators




**Model 71V (Ivory)
12-Hour Timer**

- Operates continuously or for any set period up to 12 hours
- Fits single-gang box
- 120 VAC, 20 Amp or 240 VAC, 10 Amp capacity
- For use with all Broan fans and heaters within Amp rating




**Model 72V (Ivory), 72W (White)
Electronic Variable Speed Control (6 Amp)**

- Rotary dial for variable selection of fan speed and sound level
- Positive on/off action
- Fits single-gang box
- Built-in radio noise suppressor
- Switched wire included for additional use if desired (120 VAC, 6 Amp)
- For use with all Broan fans within Amp rating except ceiling paddle fans
- Do not use with impedance protected motor




**Model 77DV (Ivory), 77DW (White)
Four-Function Control**

- Specially designed for use with Broan SensAire® and Designer Series fan/lights
- Separate switches control fan (on/off/auto), light (on/off), and night-light (on/off)
- 120 VAC, Amps each rocker = 15, 15, 5 (20 Amp total)
- Fits single-gang opening
- Includes switch function labels




**Model 78V (Ivory), 78W (White)
Ceiling Paddle Fan Speed Control**

- Four-position speed selection
- Fits single-gang box
- 120 VAC, 1.5 Amp
- For use with all Broan ceiling paddle fans




**Model 79V (Ivory), 79W (White)
Ceiling Paddle Fan Speed and Light Control**

- Four-position speed selection
- Hi-Off-Low light control
- Fits single-gang box
- 120 VAC, 1.5 Amp fan control; 300 watt maximum light
- For use with all Broan ceiling paddle fans and light kits




**Model 269VL (Ivory), 269WL (White)
Two-Function Control with Indicator**

- Red light indicates power is on
- Specially designed for use with Broan Solitaire® Ultra Silent™ fans and an auxiliary light source
- Fits two-gang box
- 120 VAC, 20 Amp lighted switch; 120/240/277 VAC, 15 Amp unlighted switch




**Model 685VL (Ivory), 685WL (White)
Three-Function Control with Indicator**

- Red light indicates power is on
- Specially designed for use with Broan Solitaire® Ultra Silent™ fans /lights
- Fits two-gang box
- 120 VAC, 20 Amp lighted switch; 120 VAC, 15 Amp each unlighted switch (20 Amp total)



**Model DH100W
Dehumidistat**

- Fits single-gang box
- Variable setting from 20% to 80% relative humidity
- Dual voltage (24V/120V)
- Usage guide included



**Model T24H
24 Hour Programmable Timer**

- Select ON/OFF times in 20 minute increments
- Manual override slide switch
- Fits single-gang box
- Clock input: 120 VAC, 60 HZ
- Output contacts: 15 Amp 1875 Watt Resistive 8 Amp Inductive 1350 Watt Tunsten 1/2 HP motor