


## 825 Series Perforated T-Bar Adjustable Curved Blade

### Standard:


- Individually adjustable curved blade T-Bar lay in diffuser with concealed hinges
- Hinged Perforated face
- Spring release face for easy access to adjust curved blades
- 2x2 galvaneal steel panel with seismic support hangers
- Round No Labor Collar sizes, 6, 7, 8, 9, 10, 12, 14, 16, 18 & 20"
- Soft White

### Optional:


- ☐ Modular core fixed blade diffuser with field adjustable air patterns (825MA)
- ☐ Field installable Bowtie Damper (BD) on 6" thru 14" round collar
- ☐ Factory installed Opposed Radial Damper (825-OR) sizes 6"-14"
- ☐ Square Collar
- ☐ Steel opposed blade damper available on square collar only (825-O)
- ☐ TVB - Thermal Vapor Blanket: 1" thick 2 x 2 foil faced self adhesive insulation blanket



825 OR




825



825 BD

Open

Closed



PROJECT

SUBMITTAL REVIEW

LOCATION

ENGINEER

ARCHITECT

CONTRACTOR