

V-BELTS

OIL & HEAT RESISTANT

Rugged polyester cord and neoprene construction with specially treated natural and synthetic elastomeric compounds make the **MAX-DRIVE** V-belt the ideal choice for heavy loads under extreme heat or for constant exposure to oil.

When replacing a V-belt, always clean pulley grooves and check that shafts are parallel and pulley alignment is correct.

	Standard V-Belt Types		
	3L	5L	
W	3/8"	1/2"	21/32"



Outside Length	WP No.		
(inches)	3L	4L	5L
20	S30-20	S40-20	-
21	S30-21	S40-21	-
22	S30-22	S40-22	-
23	S30-23	S40-23	S50-23
24	S30-24	S40-24	S50-24
25	S30-25	S40-25	S50-25
26	S30-26	S40-26	S50-26
27	S30-27	S40-27	S50-27
28	S30-28	S40-28	S50-28
29	S30-29	S40-29	S50-29
30	S30-30	S40-30	S50-30
31	S30-31	S40-31	S50-31
32	S30-32	S40-32	S50-32
33	S30-33	S40-33	S50-33
34	S30-34	S40-34	S50-34
35	S30-35	S40-35	S50-35
36	S30-36	S40-36	S50-36
37	S30-37	S40-37	S50-37
38	S30-38	S40-38	S50-38
39	S30-39	S40-39	S50-39

Outside Length		W P No.	
(inches)	3L	4L	5L
40	S30-40	S40-40	S50-40
41	S30-41	S40-41	S50-41
42	S30-42	S40-42	S50-42
43	S30-43	S40-43	S50-43
44	S30-44	S40-44	S50-44
45	S30-45	S40-45	S50-45
46	S30-46	S40-46	S50-46
47	S30-47	S40-47	S50-47
48	S30-48	S40-48	S50-48
49	S30-49	S40-49	S50-49
50	S30-50	S40-50	S50-50
51	S30-51	S40-51	S50-51
52	S30-52	S40-52	S50-52
53	S30-53	S40-53	S50-53
54	S30-54	S40-54	S50-54
55	S30-55	S40-55	S50-55
56	S30-56	S40-56	S50-56
57	S30-57	S40-57	S50-57
58	S30-58	S40-58	S50-58
59	S30-59	S40-59	S50-59
60	S30-60	S40-60	S50-60

SPECIAL FOR LENNOX BURNER

W P No.	Ref. No.	Lennox Burner No.	Belt Type	Outside Length
S20-16	VB-1049	DV-1049	2L - Cogged	16"

Westwood ceramic fibre chambers

SOUND ABSORBING • RED HOT IN SECONDS • FIRES DRY • 2,300° - 3,000°F

WET COMBUSTION CHAMBER LINERS - Sealed in a plastic bag and individually boxed*

W No.	Ref. No.	Туре		GPH	Description and Representive Picture
\$70-9 \$70-10 \$70-11 \$70-12 \$70-13 \$70-15	#9 #10 #11 #12 #13 #15	Wet	Westwood Round - Preshaped	.5075 .85 - 1.00 1.10 - 1.25 1.35 - 1.50 1.65 - 1.85 2.00 - 2.50	9" diameter, 12" high 10" diameter, 12" high 11" diameter, 12" high 12" diameter, 12" high 13" diameter, 14" high 15" diameter, 14" high
\$70-25 \$70-27	#135 #200	Wet	Westwood Rect Preshaped	.75 - 1.35 1.35 - 2.00	14" x 11" x 12" 14" x 12" x 12"
\$70-30 \$70-35 \$70-40 \$70-45	#1 #2 #3 #4	Wet	Westwood Flat sheet(s)	1.25 2.50 2.65 1.25	(1) - 14" x 48" (1) - 14" x 48" (1) - 16" x 16" (1) - 16" x 48" (1) - 16" x 16" (1) - 16" x 48"


^{*}Wet chambers have a shelf life and should be ordered such that they are not held in inventory longer than 6 months.

J-M Cerafelt[™] Dry Refractory Liners

DRY COMBUSTION CHAMBER LINERS

W No.	Ref. No.		Туре	GPH	Description and Representive Picture
\$70-50 \$70-51 \$70-52	141608 141612 144824	Dry	Cerafelt blanket		1/4" x 16" x 8 ft. 1/4" x 16" x 12 ft. 1/4" x 48" x 25 ft.
S70-60	SS Kit	Dry	Cerafelt SS Kit (For lining burned out stainless steel combustion chambers)	.50 - 1.75	(1) - 14" x 48" (1) - 16" x 33" (8) - Stainless Steel Clips

S2 rev. 1-1-09



Westwood

HIGH TEMPERATURE ROPE

NON-ASBESTOS • KNITTED FIBERGLASS

This strong, flexible, resilient knit-braided rope is ideal for industrial boilers, cast iron boilers, wood burning stoves, ovens, and furnaces.

Will not "bloom" or untwist like braided twisted glass rope. Made of 100% texturized fiberglass, it will not burn or support combustion. Resists temperatures to 1,000° F.




NON-ASBESTOS HIGH TEMPERATURE ROPE

W P No.	Туре	Description	Length
S70-101	Round	1/4" diameter	10 ft.
S70-102	Round	1/4" diameter	25 ft.
S70-104	Round	3/8" diameter	10 ft.
S70-106	Round	3/8" diameter	25 ft.
S70-108	Round	1/2" diameter	10 ft.
S70-110	Round	1/2" diameter	25 ft.
S70-111	Round	3/4" diameter	10 ft.
S70-112	Round	3/4" diameter	25 ft.
S70-114	Round	1" diameter	10 ft.
S70-116	Round	1" diameter	25 ft.
S70-140	Flat	1" wide x 1/8" thick	25 ft.
S70-142	Flat	1" wide x 1/8" thick with adhesive backing	100 ft.
S70-150	Flat	2" wide x 1/8" thick	25 ft.
S70-152	Flat	2" wide x 1/8" thick with adhesive backing	100 ft.

Other types and sizes of high temperature materials are available on special order. Consult the factory for price and availability.

BECKETT BURNER FLANGE GASKET

W P No.	Description	
S70-170	Gasket for Beckett and Aero burner flange 8-1/2" OD x 3-5/16" ID	



Westwood ONE PIECE MOTOR COUPLINGS

HEAVY DUTY FOR GENERAL USE ON BURNERS AND MOTOR DRIVEN EQUIPMENT



Rugged, precision machined end pieces are held in place by heavy steel collars. Set screws at each end insure that there is no slippage on the shaft flats. Quiet, noise and vibration absorbing, these premium couplings out-perform conventional couplings where misalignment exists or where punishing service is the norm. Available for 1/2" x 7/16" and 1/2" x 5/16" shaft sizes, or 7/16" shaft x spline socket.

ONE PIECE COUPLINGS


Length _	W _P No.					
Lengin	1/2" x 7/16"	1/2" x 5/16"	7/16" x Spline			
2"	S80-200*	S81-200*	-			
2-3/8"	S80-237	S81-237*	-			
2-1/2"	S80-250*	S81-250*	-			
3"	S80-300*	S81-300*	S82-300*			
3-1/4"	S80-325	S81-325*	S82-325			
3-3/8"	S80-337	S81-337*	S82-337			
3-1/2"	S80-350*	S81-350	S82-350			
4"	S80-400*	S81-400	S82-400*			
4-1/2"	S80-450*	S81-450	S82-450			
5"	S80-500	S81-500	S82-500*			
5-1/2"	S80-550	S81-550	S82-550			
6"	S80-600	S81-600	S82-600			
6-1/2"	S80-650	S81-650	S82-650			
7"	S80-700	S81-700	S82-700			
7-1/2"	S80-750	S81-750	S82-750			
8"	S80-800	S81-800	S82-800			

^{*} Included in One Piece Coupling Kit No. S83-200, shown below

REDUCER BUSHING & COUPLING KIT

W _P No.	Ref. No.	Description
\$83-10 \$83-200	Reducer Bushing 1890	5/16" I.D. x 7/16" O.D. bushing One piece coupling kit containing those couplings marked with an asterisk above, plus (6) S83-10 reducer bushings

S4 rev. 7-7-04



Westwood

Nylo-Flex™ BURNER COUPLINGS

EASILY INSTALLED 3 PIECE COUPLING • NO SET SCREWS





Cut



Assemble

Chosen by top service professionals and original equipment (oem) burner manufacturers. Three piece design allows for custom fit in all installations.

Nylo-Flex™ COMPONENTS

W P No.	Reference No.	Description and Representive Picture		
\$85-6 \$85-10 \$85-12 \$85-15 \$85-30	6" Nyloshaft 10" Nyloshaft 12" Nyloshaft 15" Nyloshaft 30" Nyloshaft	Nylo- $Flex$ [™] 6" Nyloshaft center piece Nylo- $Flex$ [™] 10" Nyloshaft center piece Nylo- $Flex$ [™] 12" Nyloshaft center piece Nylo- $Flex$ [™] 30" Nyloshaft center piece		
\$85-100 \$85-110 \$85-120 \$85-130	Red End Fitting Blue End Fitting Black End Fitting TA	Nylo-Flex [™] 5/16" shaft size end piece, RED Nylo-Flex [™] 7/16" shaft size end piece, BLUE Nylo-Flex [™] 1/2" shaft size end piece, BLACK Nylo-Flex [™] Torrington adapter, 1/2" shaft		

Nylo-Flex™ OEM SPEC COUPLINGS*


Two end pieces, plus a Nyloshaft correctly cut to OEM specs



W P No.	Description
S85-200	Nylo-Flex [™] Pre-cut Coupling for Beckett AF (2454), 1/2" & 5/16" Ends, 3-13/32" Nyloshaft
S85-210	Nylo-Flex [™] Pre-cut Coupling for Beckett (2290), 1/2" & 5/16" Ends, 2-7/8" Nyloshaft
S85-220	<i>Nylo-Flex</i> [™] Pre-cut Coupling for Carlin 99-100 (99RA10208), $1/2$ " & $5/16$ " Ends, $2-3/16$ " <i>Nyloshaft</i>
S85-222	Nylo-Flex [™] Pre-cut Coupling for Carlin (99RA5220), 1/2" & 7/16" Ends, 3-1/16" Nyloshaft
S85-223	Nylo-Flex [™] Pre-cut Coupling for Carlin CRDA (1020J), 1/2" & 7/16" Ends, 2-3/4" Nyloshaft
S85-224	Nylo-Flex [™] Pre-cut Coupling for Carlin 1020 (A Pump), 1/2" & 5/16" Ends, 2-11/32" Nyloshaft
S85-225	Nylo-Flex [™] Pre-cut Coupling for Ducane (B1011503), 1/2" & 5/16" Ends, 3-13/16" Nyloshaft
S85-227	Nylo-Flex [™] Pre-cut Coupling for Lennox (65A4101), 1/2" & 5/16" Ends, 3-5/8" Nyloshaft
S85-229	<i>Nylo-Flex</i> ^{m} Pre-cut Coupling for Wayne E (13279), 1/2" & 5/16" Ends, 4-5/16" <i>Nyloshaft</i>
S85-230	Nylo-Flex ^{M} Pre-cut Coupling for Wayne (13424), 1/2" & 5/16" Ends, 3-13/16" Nyloshaft
S85-231	<i>Nylo-Flex</i> [™] Pre-cut Coupling for Wayne M, $1/2$ " & $5/16$ " Ends, $3-1/4$ " <i>Nyloshaft</i>

^{*} Each coupling individually sealed in a plastic bag and labeled





Westwood

Nylo-Flex[™] BURNER COUPLINGS




THE WIDEST SELECTION TO MEET ALL SERVICING NEEDS



Nylo-Flex™ COUPLING KITS

		Quantit	y of End	Pieces	Nyloshaft	S85-130	T100-300	T100-310	Molded
W P No.	Ref. No.	1/2"	7/16"	5/16"	Quantity & Length	Torrington Adapter	Coupler Popper™	Coupling Cutter	Plastic Box
S85-500	#88	1	1	1	1 - 6"	-	-	-	-
S85-502	-	1	1	1	1 - 12"	-	-	-	-
S85-510	#99A	2	2	1	1 - 6"	-	-	-	-
S85-520	#101	2	1	2	1 - 6"	-	-	-	-
S85-525	-	8	6	5	6 - 6"	-	-	-	-
S85-530	#1240	16	8	8	8 - 9"	-	-	-	YES
S85-540	#1240C	16	8	8	8 - 9"	-	-	-	-
S85-550	#1242	16	8	8	8 - 9"	-	YES	YES	YES
S85-560	#1250	12	12	5	12 - 6"	5	-	-	-
S85-570	#1251	12	12	5	12 - 6"	5	YES	-	-

\$6 rev. 5-1-07





TUNE-UP & ELECTRODE KITS

Ref. No.

₩ No.

BURNEF	П	E-UP	19
Uanu	Ĺ		
	- Secretarial	ľ	

No. S88-10

ELECTRODE

\triangle	

twood KIT	
1	

No. \$88-20

Г				
			TUNE-UP KIT for Beckett AF,	AFG, AR, SF, SR (up to 9" air tube)
0	S88-10	BK5780	2 - Electrode assemblies 1 - 12" oil line assembly 1 - Pump coupling kit S85-500	2 - Extension rods with nuts 1 - TG-99 tip setting gauge 2 - Hex connectors
			TUNE-UP KIT for Beckett AF,	AFG, AR, SF, SR (up to 9" air tube)
	S88-12	NBK5780	2 - Electrode assemblies 1 - 12" oil line assembly 1 - Pump coupling kit S85-500 2 - Extension rods with nuts	1 - TG-99 tip setting gauge 1 - NAS gauge [™] B-1 nozzle gauge 2 - Hex connectors
			TUNE-UP KIT for Beckett AF,	AFG, AR, SF, SR (over 9" air tube)
	S88-14	BK5782	2 - Electrode assemblies 1 - 12" oil line assembly 2 - E5-2M4 insulators 1 - Pump coupling kit S85-500	2 - Extension rods with nuts 1 - TG-99 tip setting gauge 2 - Hex connectors
			TUNE-UP KIT for Beckett AF,	AFG, AR, SF, SR (over 9" air tube)
	S88-16 NBK5782		2 - Electrode assemblies 1 - 12" oil line assembly 2 - E5-2M4 insulators 1 - Pump coupling kit S85-500	2 · Extension rods with nuts 1 · TG-99 tip setting gauge 1 · NAS gauge [™] B· 1 nozzle gauge 2 · Hex connectors
			ELECTRODE KIT for Pockett	AF AFC CF CD (up to O'' air tuba)
			ELECTRODE KIT TOT DECKELL.	AF, AFG, SF, SR (up to 9" air tube)
	S88-20	W5780	2 - Electrode assemblies 2 - Extension rods with nuts	2 · Hex Connectors 1 · TG-99 tip setting gauge
		W5780	2 - Electrode assemblies	2 - Hex Connectors 1 - TG-99 tip setting gauge
	\$88-20 \$88-22	W5780 W5781	2 - Electrode assemblies 2 - Extension rods with nuts	2 - Hex Connectors 1 - TG-99 tip setting gauge
			2 - Electrode assemblies 2 - Extension rods with nuts ELECTRODE KIT for Beckett 2 - Electrode assemblies 2 - Extension rods with nuts	2 - Hex Connectors 1 - TG-99 tip setting gauge A and S (up to 9" air tube)
			2 - Electrode assemblies 2 - Extension rods with nuts ELECTRODE KIT for Beckett 2 - Electrode assemblies 2 - Extension rods with nuts	2 · Hex Connectors 1 · TG-99 tip setting gauge A and S (up to 9" air tube) 2 · Hex Connectors
	S88-22 S88-24	W5781 W5782	2 - Electrode assemblies 2 - Extension rods with nuts ELECTRODE KIT for Beckett 2 - Electrode assemblies 2 - Extension rods with nuts ELECTRODE KIT for Beckett 2 - Electrode assemblies 2 - Extension rods with nuts	2 · Hex Connectors 1 · TG-99 tip setting gauge A and S (up to 9" air tube) 2 · Hex Connectors AF, AFG, SF, SR (over 9" air tube) 2 · Hex Connectors 1 · TG-99 tip setting gauge
	S88-22	W5781	2 - Electrode assemblies 2 - Extension rods with nuts ELECTRODE KIT for Beckett 2 - Electrode assemblies 2 - Extension rods with nuts ELECTRODE KIT for Beckett 2 - Electrode assemblies 2 - Extension rods with nuts 2 - Insulators	2 · Hex Connectors 1 · TG-99 tip setting gauge A and S (up to 9" air tube) 2 · Hex Connectors AF, AFG, SF, SR (over 9" air tube) 2 · Hex Connectors 1 · TG-99 tip setting gauge
	S88-22 S88-24	W5781 W5782	2 - Electrode assemblies 2 - Extension rods with nuts ELECTRODE KIT for Beckett 2 - Electrode assemblies 2 - Extension rods with nuts ELECTRODE KIT for Beckett 2 - Electrode assemblies 2 - Extension rods with nuts 2 - Insulators ELECTRODE KIT for Beckett 2 - Electrode assemblies 2 - Extension rods with nuts 2 - Extension rods with nuts	2 · Hex Connectors 1 · TG-99 tip setting gauge A and S (up to 9" air tube) 2 · Hex Connectors AF, AFG, SF, SR (over 9" air tube) 2 · Hex Connectors 1 · TG-99 tip setting gauge AQ and S (over 9" air tube) 2 · Insulators


Description

Packaging may vary from that shown



Westwood
ELECTRODE KIT
46 44
T T
U U

₩ No. **S88-36**



No. \$88-38



₩ No. **S88-74**

TUNE-UP	& ELECTR	ODE KITS (Continued)	
₩ _P No.	Ref. No.	Descrip	otion
		ELECTRODE KIT for Beckett A	AF II, HLX (up to 9" air tube)
S88-32	51484U	2 - Electrode assemblies 2 - Extension rods with nuts	2 - Hex Connectors 1 - TG-99 tip setting gauge
		ELECTRODE KIT for Beckett /	AF II, FBX (up to 9" air tube)
S88-34	51670U	2 - Electrode assemblies 2 - Extension rods with nuts	2 - Hex Connectors 1 - TG-99 tip setting gauge
		ELECTRODE KIT for Beckett AF, A	AFG, AR, SF, SR (up to 9" air tube)
S88-36	BK-1	2 - Beckett 1510 electrodes 2 - 3/16" x 6" buss bar rods	2 - 10-32 nuts 2 - Hex Connectors
		ELECTRODE KIT for Beckett AF,	AFG, AR, SF, SR (all size air tube)
S88-38	BK-2	2 - Beckett 1510 electrodes 2 - 3/16" x 13" buss bar rods 2 - E5-2M4 insulators	2 - 10-32 nuts 2 - Hex Connectors
		TUNE-UP KIT for Carlin 98 - 1	02, Elite, 201CRD, 301CRD
S88-50	CK 780	2 - Electrode assemblies 1 - 12" oil line assembly 1 - Red tip setting gauge	1 - Yellow tip setting gauge 1 - Pump coupling kit S85-500 1 - Instructions
_		TUNE-UP KIT for We	eil McLain burner
S88-60	WMK-100	1 - One piece electrode assembly 2 - Ignition cable leads	1- Coupling 1 - Oil line assembly
		TUNE-UP KIT for Wayne ER, ERA, E	CH, EHA, EHASR, M, MSR, MH, OE, OEA
S88-70 Genuine Wayne	31156	2 - Electrode stems 2 - Electrode assemblies w/insul. 2 - Insulator bushings 2 - Buss bars (8") 1 - Buss bar support	1 - Oil line assembly 1 - Coupling 1 - "J" pump coupling end 1 - 90° nozzle line flare elbow
S88-72	211EGW	TUNE-UP KIT for Wayne ER, ERA, E	EH, EHA, EHASR, M, MSR, MH, OE, OEA
300-72	31156W	Same components as \$88-70, n	nanufactured by Westwood
		TUNE-UP KIT for Wayne	Blue Angel model HS
S88-74 Genuine Wayne	31157	2 - Electrode assemblies w/buss bars 1 - Electrode support 1 - Buss bar support 1 - Oil line assembly	1 - Coupling 1 - "J" pump coupling end 1 - 90° nozzle line flare elbow 1 - Gun setting gauge
S88-76	31157W	TUNE-UP KIT for Wayne	Blue Angel model HS
000-70	311377	Same components as S88-74, n	nanufactured by Westwood

Packaging may vary from that shown

Please order by P No.


S8



Westwood

BLOWER WHEELS

Precision balanced general purpose blower wheel ideal for oil burners. Blade strip is continuous and roll-locked front and back.



BLOWER WHEELS (Rotation as viewed from closed end)

CI	W	CC	CW		14/	Fits	
W P No.	Ref. No.	WP No.	Ref. No.	D	VV	shaft size	Comments
	STAN	DARD					
S90-10	4030	-	-	4"	3"	1/2"	
S90-12	4230	-	-	4-1/4"	3"	1/2"	
S90-14	4235	-	-	4-1/4"	3-1/2"	1/2"	
S90-16	4725	-	-	4-3/4"	2-1/2"	1/2"	
S90-18	4729	S91-18	4729-1	4-3/4"	3"	1/2"	
S90-20	4734	S91-20	4734-1	4-3/4"	3-1/2"	1/2"	
S90-22	5220	S91-22	5220-1	5-1/4"	2"	1/2"	
S90-24	5225	S91-24	5225-1	5-1/4"	2-1/2"	1/2"	
S90-26	5229	S91-26	5229-1	5-1/4"	3"	1/2"	
S90-28	5234	S91-28	5234-1	5-1/4"	3-1/2"	1/2"	
S90-30	5729	S91-30	5729-1	5-3/4"	3"	1/2"	
S90-32	5734	S91-32	5734-1	5-3/4"	3-1/2"	1/2"	
S90-34	5738	S91-34	5738-1	5-3/4"	3-7/8"	1/2"	
S90-36	6325	-	-	6-1/4"	2-1/2"	1/2"	
S90-38	6329	S91-38	6329-1	6-1/4"	3"	1/2"	
S90-40	6334	S91-40	6334-1	6-5/16"	3-1/2"	1/2"	
S90-42	6338	S91-42	6338-1	6-1/4"	3-7/8"	1/2"	
S90-44	6342	S91-44	6342-1	6-1/4"	4-1/4"	1/2"	
S90-46	6346	-	-	6-1/4"	4-5/8"	1/2"	
-	-	S91-48	7243-1	7"	4-1/4"	1/2"	
	SPE	CIAL	1				
S90-60	475-243	-	-	4-3/4"	2-7/16"	1/2"	Outside hub
S90-62	475-287	-	-	4-3/4"	2-7/8"	1/2"	Lovejoy prongs
S90-64	575-287	-	-	5-3/4"	2-7/8"	1/2"	Lovejoy prongs
S90-66	625-400	-	-	6-1/4"	4"	1"	Cast hub
S90-68	951-78	-	-	7"	4"	1"	Heavy braces
S90-70	951-81	-	-	9-3/16"	5"	5/8"	Heavy braces
_	-	S91-72	951-170	9-3/16"	5"	7/8"	Heavy braces
-	-	S91-74	951-57	11-3/4"	6"	1-1/8"	Heavy braces

PRESSURE GAUGES



PRESSURE


W P No.	Ref. No.	Mount	Face	Range	W P No.	Ref. No.	Mount	Face	Range
S100-100	146010	1/8" CBM	1-1/2"	0-15 PSI	S100-142	47738	1/4" LM	2-1/2"	0-30 PSI
S100-102	146011	1/8" CBM	1-1/2"	0-30 PSI	S100-144	47495	1/4" LM	2-1/2"	0-60 PSI
S100-104	146013	1/8" CBM	1-1/2"	0-100 PSI	S100-146	45331	1/4" LM	2-1/2"	0-100 PSI
S100-106	49488	1/4" CBM	2"	0-30 PSI	S100-148	48365	1/4" LM	2-1/2"	0-160 PSI
S100-108	47615	1/4" LM	2"	0-15 PSI	S100-150	46913	1/4" LM	2-1/2"	0-200 PSI
S100-110	46644	1/4" LM	2"	0-30 PSI	S100-152	45765	1/4" LM	2-1/2"	0-300 PSI
S100-112	45764	1/4" LM	2"	0-60 PSI	S100-154	49611	1/4" LM	2-1/2"	0-400 PSI
S100-114	45330	1/4" LM	2"	0-100 PSI	S100-156	46648	1/4" LM	2-1/2"	0-600 PSI
S100-116	46912	1/4" LM	2"	0-160 PSI	S100-158	5504	1/4" LM	3-1/2"	0-30 PSI
S100-118	47101	1/4" LM	2"	0-200 PSI	S100-160	5506	1/4" LM	3-1/2"	0-60 PSI
S100-120	46778	1/4" LM	2"	0-300 PSI	S100-162	5508	1/4" LM	3-1/2"	0-100 PSI
S100-122	47492	1/4" LM	2"	0-400 PSI	S100-164	5510	1/4" LM	3-1/2"	0-160 PSI
S100-124	47493	1/4" LM	2"	0-600 PSI	S100-166	5512	1/4" LM	3-1/2"	0-200 PSI
S100-126	52420	1/8" LM	2"	0-15 PSI	S100-168	5514	1/4" LM	3-1/2"	0-300 PSI
S100-128	47490	1/8" LM	2"	0-30 PSI	S100-170	5515	1/4" LM	3-1/2"	0-400 PSI
S100-130	52576	1/8" LM	2"	0-60 PSI	S100-172	5516	1/4" LM	3-1/2"	0-600 PSI
S100-132	47491	1/8" LM	2"	0-100 PSI	S100-174	5551	1/4" LM	4-1/2"	0-60 PSI
S100-134	48302	1/8" LM	2"	0-160 PSI	S100-176	5554	1/4" LM	4-1/2"	0-100 PSI
S100-136	46645	1/8" LM	2"	0-200 PSI	S100-178	5561	1/4" LM	4-1/2"	0-200 PSI
S100-138	48363	1/8" LM	2"	0-300 PSI	S100-180	5563	1/4" LM	4-1/2"	0-300 PSI
S100-140	47102	1/4" LM	2-1/2"	0-15 PSI					

PRESSURE GAUGES - LIQUID FILLED - Stainless steel case



W P No.	Ref. No.	Mount	Face	Range	W P No.	Ref. No.	Mount	Face	Range
S100-200	166664	1/8" CBM	1-1/2"	0-30 PSI	S100-238	165295	1/4" CBM	2"	0-1000 PSI
S100-202	166665	1/8" CBM	1-1/2"	0-60 PSI	S100-240	165296	1/4" LM	2-1/2"	0-30 PSI
S100-204	166666	1/8" CBM	1-1/2"	0-100 PSI	S100-242	165297	1/4" LM	2-1/2"	0-60 PSI
S100-206	166667	1/8" CBM	1-1/2"	0-160 PSI	S100-244	165298	1/4" LM	2-1/2"	0-100 PSI
S100-208	166668	1/8" CBM	1-1/2"	0-300 PSI	S100-246	165299	1/4" LM	2-1/2"	0-160 PSI
S100-210	166669	1/8" CBM	1-1/2"	0-1000 PSI	S100-248	165300	1/4" LM	2-1/2"	0-300 PSI
S100-212	165282	1/4" LM	2"	0-30 PSI	S100-250	165301	1/4" LM	2-1/2"	0-600 PSI
S100-214	165283	1/4" LM	2"	0-60 PSI	S100-252	165302	1/4" LM	2-1/2"	0-1000 PSI
S100-216	165284	1/4" LM	2"	0-100 PSI	S100-254	165377	1/4" LM	2-1/2"	0-2000 PSI
S100-218	165285	1/4" LM	2"	0-160 PSI	S100-256	165378	1/4" LM	2-1/2"	0-3000 PSI
S100-220	165286	1/4" LM	2"	0-300 PSI	S100-258	165303	1/4" CBM	2-1/2"	0-30 PSI
S100-222	165287	1/4" LM	2"	0-600 PSI	S100-260	165304	1/4" CBM	2-1/2"	0-60 PSI
S100-224	165288	1/4" LM	2"	0-1000 PSI	S100-262	165305	1/4" CBM	2-1/2"	0-100 PSI
S100-226	165289	1/4" CBM	2"	0-30 PSI	S100-264	165306	1/4" CBM	2-1/2"	0-160 PSI
S100-228	165290	1/4" CBM	2"	0-60 PSI	S100-266	165307	1/4" CBM	2-1/2"	0-300 PSI
S100-230	165291	1/4" CBM	2"	0-100 PSI	S100-268	165308	1/4" CBM	2-1/2"	0-600 PSI
S100-232	165292	1/4" CBM	2"	0-160 PSI	S100-270	165309	1/4" CBM	2-1/2"	0-1000 PSI
S100-234	165293	1/4" CBM	2"	0-300 PSI	S100-272	165380	1/4" CBM	2-1/2"	0-2000 PSI
S100-236	165294	1/4" CBM	2"	0-600 PSI	S100-274	165381	1/4" CBM	2-1/2"	0-3000 PSI

1/4" = 1/4"- NPT pipe thread 1/8" = 1/8"- NPT pipe thread CBM = Center back mount LM = Low mount LBM = Low back mount



LOW PRESSURE DIAPHRAGM GAUGES

W P No.	Ref. No.	Mount	Face	Range	W P No.	Ref. No.	Mount	Face	Range
S100-300	161963	1/4" LM	2-1/2"	15" WC	S100-318	161971	1/4" LM	2-1/2"	10 PSI
S100-302	161964	1/4" LM	2-1/2"	30" WC	S100-320	161972	1/4" LM	2-1/2"	20 oz35" WC
S100-304	162787	1/4" LM	2-1/2"	60" WC	S100-322	21551	1/4" CBM	2-1/2"	15" WC
S100-306	161965	1/4" LM	2-1/2"	100" WC	S100-324	21552	1/4" CBM	2-1/2"	35" WC
S100-308	161966	1/4" LM	2-1/2"	200" WC	S100-326	75995	1/4" CBM	2-1/2"	60" WC
S100-310	161967	1/4" LM	2-1/2"	20 oz.	S100-328	75991	1/4" CBM	2-1/2"	20 oz.
S100-312	161968	1/4" LM	2-1/2"	32 oz.	S100-330	21553	1/4" CBM	2-1/2"	36 oz.
S100-314	161969	1/4" LM	2-1/2"	36 oz.	S100-332	21554	1/4" CBM	2-1/2"	5 PSI
S100-316	161970	1/4" LM	2-1/2"	5 PSI	S100-334	75996	1/4" CBM	2-1/2"	10 PSI



COMPOUND GAUGES

W P No.	Ref. No.	Mount	Face	Range	W P No.	Ref. No.	Mount	Face	Range
S100-400	47925	1/8" LM	2"	30"-60 PSI	S100-408	46646	1/4" LM	2-1/2"	30"-60 PSI
S100-402	49609	1/8" LM	2"	30"-150 PSI	S100-410	47411	1/4" LM	2-1/2"	30"-150 PSI
S100-404	75260	1/8" LM	2"	30"-300 PSI	S100-412	58156	1/4" LM	2-1/2"	30"-300 PSI
S100-406	47105	1/4" LM	2-1/2"	30"-30 PSI					



GAUGE ADAPTER

W P No.	Description
S100-10	1/4"-NPT (F) x 1/8"-NPT (M) Brass gauge adapter




VACUUM GAUGES

W P No.	Ref. No.	Mount	Face	Range
S100-500	47225	1/8" LM	2"	0 - 30" Hg
S100-502	47103	1/4" LM	2"	0 - 30" Hg
S100-504	47104	1/4" LM	2-1/2"	0 - 30" Hg



TEST GAUGES

W P No.	Ref. No.	Туре	Mount	Face	Range	Refrigerant Scale	For Westwood Tester
S100-280	-	Pressure*	1/8" LM	2"	0 - 300 PSI	-	T10
S100-285	-	Pressure*	1/8" LM	2-1/2"	0 - 300 PSI	-	T20
S100-290	-	Vacuum*	1/8" LM	2"	0 - 30" Hg	-	T15
S100-295	-	Vacuum*	1/8" LM	2-1/2"	0 - 30" Hg	-	T20
S100-600	169128	Refrigerant	1/8" LM	2-1/2"	30" Hg - 350 PSI	R-12, R-22, R-502	-
S100-610	169129	Refrigerant	1/8" LM	2-1/2"	0 - 500 PSI	R-12, R-22, R-502	-
S100-620	169130	Refrigerant	1/8" LM	2-1/2"	30" Hg - 350 PSI	R-134A	-
S100-630	169131	Refrigerant	1/8" LM	2-1/2"	0 - 500 PSI	R-134A	-
S100-640	169132	Refrigerant	1/8" LM	2-1/2"	30" Hg - 500 PSI	R-410A	-
S100-650	169133	Refrigerant	1/8" LM	2-1/2"	0 - 800 PSI	R-410A	-






1/4" = 1/4"- NPT pipe thread 1/8" = 1/8"- NPT pipe thread CBM = Center back mount LM = Low mount LBM = Low back mount



PRESSURE & VACUUM TESTERS starting on page T1



^{*} Liquid filled, stainless steel case

Westwood

OIL BURNER PUMP STRAINERS & GASKETS

STAINLESS STEEL MESH ● NYLON ENDS ● SONICALLY WELDED





No. S150 (Series) Suntec J, H, S




No. S160 (Series) Suntec A70




No. S170 (Series) Suntec B80, 1-3/8"



No. S180 (Series) Suntec B80, 1-5/8"



No. S150 (Series) Suntec J, H, S



No. S190 (Series) Suntec A70 & B80











No. S197-5 Danfoss

W P No.	Ref. No.	Description biofuels COMPATIBLE	
S150	JHS	Strainer for Suntec J, H, S, individually boxed w/gasket	
S150-10	-	Strainer for Suntec J, H, S, individually bagged w/gasket	
S150-12	-	"P" Strainer for Suntec J, H, S, high capacity (coarse mesh), individually bagged w/gasket	
S150-55	-	Cover gasket for Suntec J, H, S, package of 10 gaskets	
S150-60	-	Cover gasket for Suntec J, H, S, package of 50 gaskets	
S150-65	-	Cover gasket for Suntec J, H, S, package of 100 gaskets	
S160-10	-	Strainer for Suntec A70 single-stage mini pump, individually bagged w/old style gasket	
S160-12	-	Strainer for Suntec A70 single-stage mini pump, individually bagged w/new style gasket	
S170	-	Strainer for Suntec B80 two-stage mini pump, 1-3/8" long, indiv. boxed w/old style gasket	
S170-1	-	Strainer for Suntec B80 two-stage mini pump, 1-3/8" long, indiv. boxed w/new style gasket	
S180	-	Strainer for Suntec B80 two-stage mini pump, 1-5/8" long, indiv. boxed w/old style gasket	
S180-1	-	Strainer for Suntec B80 two-stage mini pump, 1-5/8" long, indiv. boxed w/new style gasket	
S190	-	Cover gasket for Suntec A70 and B80 mini pumps, old style, package of 50 gaskets	
S190-1	-	Cover gasket for Suntec A70 and B80 mini pumps, old style, package of 100 gaskets	
S190-2	-	Cover gasket for Suntec A70 and B80 mini pumps, old style, package of 10 gaskets	
S190-5	-	Cover gasket for Suntec A70 and B80 mini pumps, new style, package of 50 gaskets	
S190-6	-	Cover gasket for Suntec A70 and B80 mini pumps, new style, package of 100 gaskets	
S190-7	-	Cover gasket for Suntec A70 and B80 mini pumps, new style, package of 10 gaskets	
S195	-	Strainer for Riello pump, individually bagged w/'O' ring gasket	
S195-5	-	Cover 'O' ring gasket for Riello pump, package of 6 'O' rings	
S197	-	Strainer for Danfoss pump, individually bagged w/'O' ring gasket	
S197-5	-	Cover 'O' ring gasket for Danfoss pump, package of 6 'O' rings	

rev. 5-1-06

FUEL SYSTEM PARTS

BY-PASS PLUGS



1/16" **THREAD**

For Suntec A, B Webster M



1/8" **THREAD**

For Suntec J, H Webster R



METRIC THREAD

For RIELLO pump



No. S213 & S214 (Series)

™ No. **S211, -1**


™ No. **S211-2, -3**

No. S211-4, -5

MILLER FURNACE OIL LINE KIT

- 1 · S213-7 oil line. For Wayne Home Equip. OE, OE-LS, M-LS, MSRH, Nu-Way FM, FM-LS, FS-LS, Beckett AF-15, when burner does not have a Sundstrand A1VA 17J1600 pump.
- 1 · S213-11 oil line. For Wayne Home Equip. OE, OE-LS, Nu-Way FM, FM-LS, when burner has Sundstrand A1VA 17J1600 pump.
- 1 · 1/4" flare x 3/16" flare reducer adapter for certain Wayne OE & OE-LS burners
- 1 · 3/16" flare x 1/8" · NPT elbow for certain Wayne OE & OE-LS burners


No. S214-25





TAKE THE **MAGIC*PATCH**[™] CHALLENGE

PUT A MAGIC*PATCH AGAINST A REGULAR MAGNETIC PATCH (PAD TO PAD, HELD TOGETHER BY THE MAGNETS) AND LEAVE THEM FOR 24 HOURS. AFTER THAT TIME TEST THE MAGNETS. YOU'LL SEE WHAT MAKES THE MAGIC*PATCH, "MAGIC"




...holds like magic!

™ No. **S215, -1**

₩ No. S216

BY-PASS PLUGS, OIL LINES & FITTINGS, MAGIC-PATCH

W P No.	Ref. No.	Description
S211	-	By-Pass Plug for Suntec A, B and Webster M, 1/16"- NPT, package of 10
S211-1	-	By-Pass Plug for Suntec A, B and Webster M, 1/16"- NPT, package of 100
S211-2	-	By-Pass Plug for Suntec J, H and Webster R, 1/8" NPT, package of 10
S211-3	-	By-Pass Plug for Suntec J, H and Webster R, 1/8" NPT, package of 100
S211-4	-	By-Pass Plug for RIELLO pump, (takes 2.5mm hex key), package of 10
S211-5	-	By-Pass Plug for RIELLO pump, (takes 2.5mm hex key), package of 100
S213-5	3605	Nozzle line w/flare nuts, 3/16" O.D. copper tubing, 5" long
S213-7	3607	Nozzle line w/flare nuts, 3/16" O.D. copper tubing, 7" long
S213-8	3608	Nozzle line w/flare nuts, 3/16" O.D. copper tubing, 8" long
S213-11	3611	Nozzle line w/flare nuts, 3/16" O.D. copper tubing, 11" long
S213-12	3612	Nozzle line w/flare nuts, 3/16" O.D. copper tubing, 12" long
S213-16	3616	Nozzle line w/flare nuts, 3/16" O.D. copper tubing, 16" long
S214-12	1412	Nozzle line w/flare nuts, 1/4" O.D. copper tubing, 12" long
S214-16	1416	Nozzle line w/flare nuts, 1/4" O.D. copper tubing, 16" long
S214-25	OL-711	Oil line parts kit for Miller furnaces, (1) S213-7, (1) S213-11, (2) fittings
S215	-	Replacement nozzle line fitting for Beckett S, SR, SF series burners
S215-1	-	Replacement nozzle line fitting for Beckett A, AF, AR series burners
S216	-	MAGIC*PATCH magnetic emergency tank leak patch




S14

rev. 1-1-09

Please order by P No.

Tigerloop® Model TN



World's most advanced oil de-aerator!

After years of development, the next generation Tigerloop® oil de-aerator has arrived! With over 30 years experience and more than 3.5 million Tigerloops® installed worldwide, Tigerholm is uniquely qualified to take oil de-aeration to the next level.

More than just a problem solver!

For years, Tigerloop® has been primarily thought of as a problem solver, a "band-aid," used to easily cure air and suction line problems. But, that's only part of the story! All systems benefit from Tigerloop's® unique ability to condition the oil prior to burning. Whether it's air elimination, nozzle coking problems, vacuum reduction, oil preheating, or just the elimination of that potentially leaky return line, Tigerloop® is today's safe, economical, environmentally friendly choice for all oil supply systems.


The Advantages of Tigerloop ...

Safely Handles suction line air leaks

Removes air entrained in oil during transporting and delivery Reduces running vacuum for clear, foam-free oil at the nozzle Eliminates potential leak hazard by eliminating the return line Preheats the oil for cleaner combustion

Extends filter element life

MAX. RETU TEMPERATI MAX. INLET CONNECTION FUEL	RLE CAPACITY
P No.	Description
S220	Tigerloop® oil de-aerator, model TN, UL Listed



The New

Tigerloop®

ULTRA

The economical Tigerloop®/Spin-On filter combination that's fast and easy to install. Costs less than installing a Tigerloop® and Spin-On separately! Designed specifically for the demands of American heating systems.



Costs less than installing a Tigerloop® and Spin-On separately!

Technical Information

MAX. NOZZLE CAPACITY 20 GPH MAX. RETURN OIL FLOW 30 GPH TEMPERATURE RANGE 20° - 105° F MAX. INLET PRESSURE 8 PSI CONNECTIONS 1/4"- NPT (female)

$\textbf{Tigerloop}^{\texttt{@}} \ \textbf{ULTRA}^{\texttt{\tiny{TM}}} \ \textbf{OIL} \ \textbf{DE-AERATOR} \ \textbf{\&} \ \textbf{SPIN-ON} \ \textbf{FILTER}$

P No.	Description
S220-8	Tigerloop® ULTRA™ oil de-aerator & Spin-On filter, UL Listed
F100-10	Replacement Spin-On element, standard thread, see page F4

S16

rev. 1-1-09

Please order by P No.

Tigerloop® Bio™ NEW!

A standard Tigerloop® with B100 compatibility!



Technical Information

MAX. NOZZLE CAPACITY 20 GPH
MAX. RETURN OIL FLOW
TEMPERATURE RANGE20° - 105° F
MAX. INLET PRESSURE
CONNECTIONS
FUEL
Not for use with E diesel or any fuel containing Ethanel (alcohol)

P No.	Description
S220-1	Tigerloop® Bio™ oil de-aerator for biofuels to B100

Tigerloop®

ULTRA-B™ NEW

A standard Tigerloop® ULTRA™ with B100 compatibility!

Technical Information

MAX. NOZZLE CAPACITY	20 GPH
MAX. RETURN OIL FLOW	
TEMPERATURE RANGE	20° - 105° F
MAX. INLET PRESSURE	8 PSI
CONNECTIONS	. 1/4"- NPT (female)
REPLACEMENT ELEMENT	F100-10
ELEMENT MEDIA	10 Micron
ELEMENT CANISTER	EPOXY INSIDE
FUEL B100 BioHeat [®] , No.	1 & 2 HEATING OIL
Not for use with E-diesel or any fuel containing Ethanol (alcoho	ol)

P No. Description

Tigerloop[®] ULTRA[™]-**B** oil de-aerator & filter



Please order by P No.

S220-9

Tigerloop®

Combi[™],



The Tigerloop® Combi™ was developed for the low firing rate burners of Europe. It features a clear plastic bowl which houses a high efficiency sintered plastic filter element. The forerunner of the Tigerloop® ULTRA.™

Tigerloop® Combi™ OIL DE-AERATOR & FILTER

W P No.	Description
S220-4 S220-6	Tigerloop® Combi™ oil de-aerator & filter Replacement sintered plastic filter element for S220-4 (Combi)

Technical specs are the same as for the S220. See page S15

Tigerloop®

Twin





If something is good... then two are better!

The Tigerloop® **Twin™** has twice the capacity for those large commercial jobs. Get all the benefits of Tigerloop's famous de-aeration capabilities...in a bigger way! Comes complete with Westwood's commercial duty Spin-On filter.

Technical Information

MAX. NOZZLE CAPACITY 40 GPH	SPIN-ON FILTER SUPPLIED F100-1
MAX. RETURN OIL FLOW 60 GPH	REPLACEMENT ELEMENT F100-11
TEMPERATURE RANGE 20° - 105° F	ELEMENT MEDIA 30 Micron
MAX. INLET PRESSURE 8 PSI	ELEMENT CANISTER EPOXY INSIDE
TANK CONNECTION 3/8"- NPT	FUEL No. 1 & 2 HEATING OIL, B5 BioHeat®
PUMP CONNECTIONS 1/4"- NPT	Not for use with E-diesel or any fuel containing Ethanol (alcohol)

Tigerloop® Twin™ OIL DE-AERATOR & SPIN-ON FILTER

P No.	Description
S220-15	Tigerloop® Twin™ oil de-aerator & commercial duty Spin-On filter
F100-11	Replacement Spin-On element, standard thread, see page F4

S18 Please order by P No. rev. 1-1-09



GENUINE

Tigerloop®

FLEXIBLE OIL LINES



Steel Braided Covering 24" & 36" Long 145 PSI - 200°F



FLEXIBLE OIL LINES, Standard


W P No.	Description
S220-24 S220-36 S220-40 S222-36	Flexible oil line, braided steel outside covering, 1/4"- NPT (MxM), 24" long Flexible oil line, braided steel outside covering, 1/4"- NPT (MxM), 36" long Replacement fitting for flexible oil line, 3/8" inv. flare x 1/4"-NPT Flexible oil line, braided steel outside covering, 3/8" Flare (FxF), 36" long



Steel Braided Covering 24" & 36" Long 145 PSI - 200°F Color coded Red & Blue for easy identification


FLEXIBLE OIL LINES


SPECIAL FOR RIELLO



FLEXIBLE OIL LINES, Special for RIELLO burners


W P No.	Description
S221-24 S221-36	, , , , , , , , , , , , , , , , , , , ,





E-Z Connect ADAPTOR FITTING

One fitting quickly connects the 1/4"-NPT male end of flexible oil lines to 3/8" FLARE!



CHECK VALVES



₩ No. **S230**



₩ No. **S230-1**



Isolates burner components from fuel supply line pressure. Requires pump vacuum to draw oil from the tank.



1/2"- NPT

₩ No. S225

Technical Information	
MAXIMUM FLOW 20 GPH	FUEL No. 2 OR LIGHTER
TEMPERATURE RANGE 0 - 160° F	APPROVALUL LISTED
MAX. INLET PRESSURE 40 PSI	CONNECTIONS 3/8"- NPT

rev. 1-1-09


Please order by P No.

Westwood



OIL SAFETY VALVE & SPIN-ON FILTER

Combines the Suntec PRV-38P oil safety valve with the Westwood Products Ultra-10™ (10 micron) high efficiency Spin-On filter element number F100-10. This combination provides the ultimate in protection for oil supply systems and costs less than installing an oil safety valve and Spin-On separately!



Costs less than installing an Oil Safety Valve and Spin-On separately!

Technical Information


Westwood OIL SAFETY VALVE & SPIN-ON FILTER

P No.	Description
S226	Westwood oil safety valve and Spin-On filter, UL Listed
F100-10	Replacement Spin-On element, standard thread, see page F4



HEATING OIL TANK ACCESSORIES





W P No.	Description	W P No.	Description
S270 S270-1 S270-4 S270-6 S270-8	1-1/4" Vent alarm 2" Vent alarm 1-1/4" Aluminum vent cap, set screw 1-1/4" Aluminum vent cap, set screw, screen 2" Aluminum vent cap, set screw		1/2" x 3/8" Oil tank valve, straight 1/2" x 3/8" Oil tank valve, 90° angle 1-1/2" and 2" Tank gauge, 24"

UNIVERSAL DRAFT REGULATOR

Fits the most popular smoke pipe sizes.





W P No.	Ref. No.	Description
S300-300	#678	3 in 1 combination draft regulator, fits 6", 7", 8" smoke pipe

S22


rev. 5-1-07

Please order by P No.

Westwood

CRANK ARMS - SWIVELS - PUSH RODS


PRECISION MACHINED ● HEAVY DUTY ● PLATED STEEL




3·7/32" 2·23/32" -1·13/32" -1·13/32" Shaft dia.

Slotted Crank Arm

3 Hole Crank Arm





Slotted Crank Arm (shaft clamping)

Swivel


Push Rod

W P No.	Ref. No.	Shaft Dia.	Α	В	Swivel Thread x Length	Push Rod Length	Description
S300-400	ARM-3S	3/8"	3-3/16"	2-1/8"	-	-	Slotted crank arm
S300-402	ARM-5S	1/2"	3-3/16"	2-1/8"	-	-	Slotted crank arm
S300-404	ARM-3L	3/8"	4-15/16"	3-7/8"	-	-	Slotted crank arm
S300-406	ARM-5L	1/2"	4-15/16"	3-7/8"	-	-	Slotted crank arm
S300-408	ARM-14	3/8"	-	-	-	-	3 hole crank arm
S300-410	ARM-15	1/2"	-	-	-	-	3 hole crank arm
S300-412	ARM-5C	1/2"	3-19/32"	2-3/8"	-	-	Clamping crank arm
S300-414	SW-4	-	-	-	1/4-20 x 7/16"	-	Swivel
S300-416	SW-5	-	-	-	5/16-24 x 41/64"	-	Swivel
S300-418	SW-6	-	-	-	5/16-24 x 33/64"	-	Swivel
S300-420	SW-8	-	-	-	1/4-28 x 9/16"	-	Swivel
S300-422	SW-9	-	-	-	1/4-20 x 9/16"	-	Swivel
S300-424	PR-12	-	-	-	-	12"	5/16" dia. push rod
S300-426	PR-18	-	-	-	-	18"	5/16" dia. push rod
S300-428	PR-24	-	-	-	-	24"	5/16" dia. push rod
S300-430	PR-36	-	-	-	-	36"	5/16" dia. push rod
S300-432	PR-48	-	-	-	-	48"	5/16" dia. push rod

Westwood

HIGH TEMPERATURE GLASSWARE

BOROSILICATE & SODA LIME WINDOW GLASS





OBSERVATION PORTS

Clear - Soda Lime Window Glass - Male Pipe Thread Mount - 500° F

W P No.	Reference No.	Pipe Thread	Working Pressure
S305-37	OBS-38	3/8"- NPT	3,700 PSI
S305-50	OBS-50	1/2"- NPT	3,500 PSI
S305-75	OBS-75	3/4"- NPT	3,000 PSI
S305-100	OBS-100	1"- NPT	2,500 PSI
S305-125	OBS-125	1-1/4"- NPT	2,000 PSI
S305-150	OBS-153	1-1/2"- NPT	1,500 PSI

ROUND SIGHT GLASSES - Clear - Borosilicate Glass - 600° to 800° F

		W P No.				W P No.	
Diameter	1/8" Thick	3/16" Thick	1/4" Thick	Diameter	1/8" Thick	3/16" Thick	1/4" Thick
1"	S312-100	S318-100	S325-100	2-5/8"	S312-262	S318-262	S325-262
1-1/8"	S312-112	S318-112	S325-112	2-3/4"	S312-275	S318-275	S325-275
1-3/16"	S312-118	S318-118	S325-118	3"	S312-300	S318-300	S325-300
1-1/4"	S312-125	S318-125	S325-125	3-1/8"	S312-312	S318-312	S325-312
1-3/8"	S312-137	S318-137	S325-137	3-3/16"	S312-318	S318-318	S325-318
1-7/16"	S312-143	S318-143	S325-143	3-1/4"	S312-325	S318-325	S325-325
1-1/2"	S312-150	S318-150	S325-150	3-3/8"	S312-337	S318-337	S325-337
1-5/8"	S312-162	S318-162	S325-162	3-7/16"	S312-343	S318-343	S325-343
1-3/4"	S312-175	S318-175	S325-175	3-1/2"	S312-350	S318-350	S325-350
2"	S312-200	S318-200	S325-200	3-5/8"	S312-362	S318-362	S325-362
2-1/8"	S312-212	S318-212	S325-212	3-3/4"	S312-375	S318-375	S325-375
2-3/16"	S312-218	S318-218	S325-218	4"	S312-400	S318-400	S325-400
2-1/4"	S312-225	S318-225	S325-225	4-1/2"	S312-450	S318-450	S325-450
2-3/8"	S312-237	S318-237	S325-237	5"	S312-500	S318-500	S325-500
2-7/16"	S312-243	S318-243	S325-243	6"	S312-600	S318-600	S325-600
2-1/2"	S312-250	S318-250	S325-250				

Special size round, square, rectangular shapes, and colors available. Consult the factory for price and delivery.

rev. 1·1·09

Please order by P No.


BOILER & FURNACE CLEANING ITEMS

"SERVICE-SAW" BOILER SCALE BUSTING TOOL



₩ No. S400

"SOOT SABER" BOILER CLEANING TOOLS




₩ No. S402




No. S405

"SOOT SNAKE" VAC HOSE




Mo. S410

SOOT SHOVEL




No. S412

VACUUM CLEANER BAGS - Wrap around seam sealed for strength



No. S450-14, -15



When soot's involved, THE SEAM MATTERS!

WHEN BAGS INFLATE, THE ENTIRE FORCE IS PUT ON THE SEAM HOLDING THE BAG TOGETHER. OTHER BAGS RELY ON A GLUED LAP SEAM THAT CAN GIVE WAY UNDER PRESSURE.

WESTWOOD'S SEAM IS ON THE EDGE, WHICH GIVES A STRONGER, WRAP AROUND SEAL.

CLEANING TOOLS & VACUUM CLEANER BAGS

W P No.	Reference No.	Description
S400	Service-Saw	"Service-Saw" boiler scale cleaning tool, tempered steel saw blade, plastic handle
S402	-	"SOOT SABER" Heavy Duty (rigid) boiler cleaning tool, zinc coated steel, wood handle
S405	-	"SOOT SABER" Flexible boiler cleaning tool, zinc coated steel, soft vinyl handle
S410	-	"SOOT SNAKE" Flexible steel vacuum cleaner hose, 7/8" dia., 48" long, with installed
		rubber adapter to fit a standard 1-1/2" rubber vacuum cleaner hose
S412	-	Soot Shovel, 4-1/2" wide, 19-1/2" long, steel with black enamel finish
S450-14	-	Style 4464 (3-1/2 gal.) vacuum cleaner bags. Fits Mastercraft 605, 641, 1100, 6500
		and others; Sid Harvey S12. Package of 5 bags
S450-15	-	Style 4465 (5 gal.) vacuum cleaner bags. Fits Mastercraft 652, 653, 880, 990, 1005,
		1010, 1015, 1200, 7000, 13008, D6508, D6520, D6530, W6508, W6509, W6510,
		6513, and others; Sid Harvey S14. Package of 5 bags



Safety and Spill Cleanup Supplies

.llı

CLOTH



No. **S500** PAIR

Brown jersey gloves man's hand size



No. S500-2

PAIR White cotton gloves man's hand size

GOGGLES

า

NITRILE

No. S500-8

PAIR

Reusable heavy duty oil resistant

nitrile gloves, man's hand size

No. S500-4

BOX OF 100 Disposable oil resistant nitrile gloves, LARGE



™No. **S500-6**

BOX OF 100 Disposable oil resistant nitrile gloves, X-LARGE



MASKS

№ No. **S500-10**

EACH Disposable dust mask, elastic strap, not rated



GLASSES

No. S500-14

Adjustable Plastic safety glasses, clear lenses



No. S500-12

Disposable dust mask, elastic strap, N95 rated




No. S500-16

EACH

Adjustable Plastic safety glasses, smoked lenses

SHOE COVERS

SHOE COVERS



₩ No. **S500-20**

PAIR
Disposable non-woven
fabric slip-on shoe covers




BAGS

No. S500-22*

PACKAGE OF 20 7 bu. plastic (3 mil.) contractor disposal bags






No. S500-24

5 lb. BOX Rags (polo shirt material) mixed colors

SPILL KIT





№ No. **S500-26**

PACKAGE OF 100 Flat paper wipes, 13" x 13"

COVERALLS

elastic strap

PADS

No. S500-28

OIL ONLY

(ALL LIQUIDS)

No. S500-18*

EACH

Plastic splash goggles,

SOCKS



™No. S500-32

PACKAGE OF 100 PACKAGE OF 40
Absorbent pads Absorbent socks
17" x 18" x 1/8" thick 3" dia. x 48" long



™ No. S500-30*

PACKAGE OF 100

Absorbent pads
16-1/2" x 19-1/2" x 3/16" thick

PACKAGE OF 40

Absorbent socks
3" dia. x 48" long

DROP CLOTH





No. S500-36

EACH Large non-woven fabric drop cloth, water repellent

Spill Kit in Heavy Duty

Zippered Carrying Bag Contains:

1 - splash goggles

1 - pr. nitrile reusable gloves

2 - contractor bags

1 - All liquid absorbent sock

1 - Oil only absorbent sock


5 - All liquid absorbent pads

5 - Oil only absorbent pads

1 - Heavy duty clear plastic zippered carrying bag

No. S500-38

EACH Economy Spill Kit in zippered carrying bag



Full Body Coverall

Disposable, white non-woven fabric

No. **\$500-50**

No. **S500-60** X - LARGE

* Part of the S500-38 Economy Spill Kit (see listing above for quantities of each included in the kit).