

HDPE TRANSITION ACCESSORY PACK WITH GLAND

Product Features

Rubber Gasket

- Material SBR
- Standard ANSI / AWWA C111 / A21.11
- ASTM Test Methods
 - Hardness D2240-91
 - Tensile Strength & Elongation D412-92
 - Minimum Aging D572-88
 - Maximum Compression D395-89
 - NSF/ANSI Standard 61 Compliant

Ductile Iron Gland

- Material ASTM A536, Grade 65-45-12
- Standard ANSI / AWWA C153 / A21.53
- Coating Asphaltic seal coat inside and out in accordance with ANSI / AWWA C104 / A24.1


Low Alloy Steel T-Head Bolts & Nuts

- Material & Dimension ANSI / AWWA C111 / A21.11
- Extra long to accommodate HDPF Flange

Product Specifications HDPE Transition Accessory Pack works with DIPS & IPS Transitions

Includes Gland, MJ Gasket and Extra Long T-Head Bolts

PART #	SIZE
IMJAPHDIM	3"
IMJAPHDIP	4"
IMJAPHDIU	6"
IMJAPHDIX	8"
IMJAPHDI10	10"
IMJAPHDI12	12"





PROSELECT Glands, Gaskets, T-head Bolts and Mechanical Joint Accessory Packs are sold exclusively through Ferguson Enterprises and its affiliates.

Ferguson Enterprises guarantees the quality and compliance to the listed specifications.

PROSELECT is a registered trademark of Ferguson Enterprises.

Warranty and Codes

This PROSELECT product carries a 1-year limited warranty.