

PFXCCMS Series

Low Lead Dielectric Unions



Product Features

- EPDM washer
- PSU (Polysulfone) Sleeve
- Pressure rated at 250 psi at 180°F or 50 psi at 300°F
- Prevents electrolysis or galvanic action when connecting dissimilar materials
- Threads conform to ANSI B1.20.1
- Solder ends conform to ANSI B16.22
- Low lead compliant



PFXCCMS22


Model Numbers

PFXCCMS22	1/2" MIP x 1/2" Copper Sweat
PFXCCMS33	3/4" MIP x 3/4" Copper Sweat

Replacement Parts

PFDUGD	1/2" (12.7mm) EPDM Dielectric Union Gasket
PFDUGF	3/4" (19.0mm) EPDM Dielectric Union Gasket

Size	A		B		C		D	
	mm	in	mm	in	mm	in		
1/2"	35.89	1.41	65.38	2.57	15.95	0.63	1/2"	NPT
3/4"	40.77	1.61	73.71	2.90	22.30	0.88	3/4"	NPT



Warranty and Codes

This PROFLO product carries a 1-year limited warranty

