



	Type _____					
	-09	-20	-20T	-30	-33	-46
P2612	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>

Catalog No.	Finish						Dimensions (Inches)	
	Brushed Nickel	Antique Bronze	Antique Bronze	White	Cobblestone	Weathered Bronze	A	B
	-09	-20	-20T	-30	-33	-46		
P2612	-09	-20	-20T	-30	-33	-46	10-3/4	6



**Specifications:**

General

- Brushed Nickel (-09), White (-30), Cobblestone (-33) and Weathered Bronze (-46) has an Alabaster glass bowl. Antique Bronze (-20) has an etched glass bowl and the (-20T) has an etched light amber glass bowl.
- Pull chain on brushed nickel (-09) is chrome with a maple fob and white (-30) finish is chrome with a white fob, the rest are antique brass with a medium oak fob
- Utilizes (3) 40-watt candelabra based lamps. Included.

Mounting

- Universal - use with any indoor fan with a 1/8" IPS light kit mount.

Electrical

- Porcelain candelabra sockets
- Quick connect wiring to fan
- Prewired
- 190-watt limiter

Labeling

- UL listed