



Incandescent

Westport


Outdoor

Type _____

-20 -30 -31

P3883 ☐ ☐ ☐

Catalog No.	Finish			Lamping	Dimensions (Inches)	
	Antique Bronze	White	Black		A	B
P3883	-20	-30	-31	1 (m) 100w	9-1/8	10-1/4



Specifications:

General

- Clear seeded glass : 7" dia., 5-3/4" ht.
- Powder with liquid top coat Antique Bronze (-20), White (-30), Black (-31) finishes
- Ribbed details with ribbed finials
- Die-cast aluminum construction
- Companion Chain hung lantern, Post top lantern, Wall lantern, fixtures are available

Mounting

- Ceiling flush mount
- Unit covers a standard 4" hexagonal recessed outlet box: 9" dia., 1" ht.
- Mounting strap for outlet box included

Electrical

- Medium base ceramic socket
- Pre-wired

Labeling

- cCSAus Damp location listed

Progress Lighting
701 Millennium Blvd.
Greenville, South Carolina
29607

www.progresslighting.com

Rev. 01/15



Compact Fluorescent

Westport

Outdoor


Energy Star® Qualified

Type _____

-20WB -31WB

P3883 ☐ ☐

Catalog No.	Finish		Lamping	Dimensions (Inches)	
	Antique Bronze	Black		A	B
P3883	-20WB	-31WB	1-13w GU-24 (included)	9-1/8	10-1/4



Specifications:

General

- Frosted seeded glass : 7" dia., 5-3/4" ht.
- Powder with liquid top coat Antique Bronze (-20WB), Black (-31WB) finishes
- Ribbed details with ribbed finials
- Die-cast aluminum construction
- GU24 base 13w lamp (included)
- Energy Star® qualified
- Companion Chain hung lantern, Post top lantern, Wall lantern, fixtures are available

Mounting

- Ceiling flush mount
- Unit covers a standard 4" hexagonal recessed outlet box: 9" dia., 1" ht.
- Mounting strap for outlet box included

Electrical

- GU24 base socket
- Pre-wired

Labeling

- cCSAus Damp location listed



Progress Lighting
701 Millennium Blvd.
Greenville, South Carolina
29607

www.progresslighting.com

Rev. 10/13