



	Type		
	-20	-30	-31
P5682	☐	☐	☐
P5683	☐	☐	☐
P5684	☐		☐

Catalog No.	Finish			Lamping	Dimensions (Inches)			
	Antique Bronze	Textured White	Textured Black		A	B	C	D
P5682	-20	-30	-31	1-100w (m)	6-1/4	13-1/16	9-3/4	3-1/2
P5683	-20	-30	-31	1-100w (m)	9-3/8	16	11-1/4	3-1/2
P5684	-20		-31	1-100w (m)	9-3/8	30-3/4	11-3/8	18-3/8



Specifications:

General

- Etched (-20) or Clear beveled (-30, -31) glass panels
- Each glass panel replaceable
- Powdercoat Antique Bronze (-20) finish
- Painted Textured White (-30) and Textured Black (-31) finishes
- Die-cast aluminum exterior, solid brass interior components
- Cast wall plate
- CompanionChain hung lantern, Post top lantern, Wall lantern, fixtures are available

Mounting

- Wall mount
- Backplate covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included
- P5682 back plate 4-1/2" W., 7" ht.
- P5683 back plate 4-1/2" W., 7" ht.
- P5684 back plate 4-1/2" W., 7" ht.

Electrical

- Pre-wired
- Medium base ceramic socket with nickel-plated brass screw shell



Labeling

- cCSAus Wet location listed

Type _____
-20EB -31EB

P5682	☐	☐
P5683	☐	☐
P5684	☐	☐

Catalog No.	Finish		Lamping	Dimensions (Inches)			
	Antique Bronze	Textured Black		A	B	C	D
P5682	-20EB	-31EB	1-26w GU-24	6-1/4	13-1/16	9-3/4	3-1/2
P5683	-20EB	-31EB	1-26w GU-24	9-3/8	16	11-1/4	3-1/2
P5684	-20EB	-31EB	1-26w GU-24	9-3/8	30-3/4	11-3/8	18-3/8



Specifications:

General

- Etched glass panels
- Each glass panel replaceable
- Powdercoat Antique Bronze (-20) finish
- Painted Textured Black (-31) finish
- Die-cast aluminum exterior, solid brass interior components
- Cast wall plate
- CompanionChain hung lantern, Post top lantern, Wall lantern, fixtures are available

Mounting

- Wall mount
- Backplate covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box and cap nuts furnished
- P5682 back plate 4-1/2" W., 7" ht.
- P5683 back plate 4-1/2" W., 7" ht.
- P5684 back plate 4-1/2" W., 7" ht.

Electrical

- Pre-wired
- GU24 base socket

Labeling

- cCSAus Wet location listed