


6" Single Vertical Lamp Housing IC/Air-Tight


Recessed

Туре		
P83-26	ICAT	

Dimonsions (Inches)

		Diffierisions (inches)	
Catalog No.	Lamping	A B C	
P83-26ICAT	(1) 26w Triple CF (4-pin)	7-7/8 10-3/4 7-1/2	
		Ceiling Opening 6-7/8	





Specifications:

Wiring

- Universal junction box with snap-out sides
- Removable housing for field inspection of wiring
- Grounding pigtail
- Knockout free Romex clamps
- 1/2" & 3/4" Knock outs for rigid or BX fittings
- Electronic NPF 120-volt ballast with end of life protection
- Pre-installed 4-port wire quick connects

Construction

- Notched housing for chalkline alignment
- Full wrap-around plaster frame
- Removable K.O. for remodel use (P8607-01 plaster frame clips also required)
- Galvanized steel construction
- Tooless adjustment for 1/2" to 2-1/2" thick ceilings

Bar Hangers

- Integral II ga. fluted nail for wood joist construction
- Integral snap-on T-bar mounting clip
- Rigid male/female design spans 24" for suspended ceilings

- Lock to secure housing
- Captive with extension stop tab
- 90-degree mounting for tight spaces
- Joint alignment tab

Labeling

- UL-CUL listed for damp locations
- Not rated for through branch wiring, but can be daisy chained
- Complies with Washington State Energy Code (WSEC) requirement for Air tight
- Complies with California Title 24 Legislation
- IC rated

Lamp/Trim

- Trim-Lok[®] action forces trim to fit snugly against the ceiling
- Socket mounts to trim for optimum performance, and provides consistent vertical lamp position
- Single-lamp vertical 26w (4-pin) G24q-3 or GX24q-3 compact fluorescent
- Foil gasket included to complete air-tight installation

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607





6" Single Vertical Lamp Housing IC/Air-Tight/ Dimming

Recessed

Туре		
P83-26	ICATDM	

	Lamping	Dimensions (Inches)	
Catalog No.		A В С	
P83-26ICATDM	(1) 26w Triple CF (4-pin)	7-7/8 10-3/4 7-1/2 Ceiling Opening 6-7/8	





Specifications:

Wiring

- Universal junction box with snap-out sides
- Removable housing for field inspection of wiring
- Grounding pigtail
- Knockout free Romex clamps
- 1/2" & 3/4" Knock outs for rigid or BX fittings
- Electronic NPF(.80), 120-volt ballast with end of life protection. (150% THD)
- Dimming ballast down to 15% lamp output
- Ballast is compatible with most electromechanical incandescent dimming switches
- Pre-installed 4-port wire quick connects

Construction

- Notched housing for chalkline alignment
- Full wrap-around plaster frame
- Removable K.O. for remodel use (P8607-01 plaster frame clips also required)
- Galvanized steel construction
- Tooless adjustment for 1/2" to 2-1/2" thick ceilings

Bar Hangers

- Integral II ga. fluted nail for wood joist construction
- Integral snap-on T-bar mounting clip

- Rigid male/female design spans 24" for suspended ceilings
- Lock to secure housing
- Captive with extension stop tab
- 90-degree mounting for tight spaces
- Joint alignment tab

<u>Labelinc</u>

- UL-CUL listed for damp locations
- Not rated for through branch wiring, but can be daisy chained
- Complies with Washington State Energy Code (WSEC) requirement for Air tight
- Complies with California Title 24 Legislation
- IC rated

Lamp/Trim

- \bullet Trim-Lok $^{\textcircled{\scriptsize R}}$ action forces trim to fit snugly against the ceiling
- Socket mounts to trim for optimum performance, and provides consistent vertical lamp position
- Single-lamp vertical 26w (4-pin) G24q-3 or GX24q-3 compact fluorescent
- Foil gasket included to complete air-tight installation



Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607

www.progresslighting.com

Rev. 4/12



Approved Dimming Control Devices for Use with P83-26ICATDM

Progress Lighting's P83-26ICATDM is designed for compatibility with most electromechanical incandescent dimmer switches. Following is a list of switches approved by the ballast manufacturer:

Manufacturer	Series	Comments
Hunt Dimming	PS, SC, FD, SSD Simplicity	All Mark X dimmers
Leviton	IllumaTech Preset Slide,	
	IllumaTech Rotary, SureSlide	
Pass & Seymour	Scene Director, Leandro	Mark X version only
Progress Lighting	P8538-30, P8540-30	





6" Single Vertical Lamp Housing IC/Air-Tight

Recessed

Туре	
P83-ICAT	

		Dimer	nsions (I	nches)
Catalog No.	Lamping	Α	В	С
P83-ICAT	(1) 13w Quad or Triple CF (4-pin)		10-3/4 Openin	–





Specifications:

Wiring

- Universal junction box with snap-out sides
- Removable housing for field inspection of wiring
- Grounding pigtail
- Knockout free Romex clamps
- 1/2" & 3/4" Knock outs for rigid or BX fittings
- Electronic NPF 120-volt ballast with end of life protection (located inside junction box)

Construction

- Notched housing for chalkline alignment
- Full wrap-around plaster frame
- Removable K.O. for remodel use (P8607-01 plaster frame clips also required)
- Galvanized steel construction
- Tooless adjustment for 1/2" to 2-1/2" thick ceilings

Bar Hangers

- Integral II ga. fluted nail for wood joist construction
- Integral snap-on T-bar mounting clip
- Rigid male/female design spans 24" for suspended ceilings

- Lock to secure housing
- Captive with extension stop tab
- 90-degree mounting for tight spaces
- Joint alignment tab

Labeling

- UL-CUL listed for damp locations
- Not rated for through branch wiring, but can be daisy chained
- Complies with Washington State Energy Code (WSEC) requirement for Air tight
- Complies with California Title 24 Legislation
- IC rated

Lamp/Trim

- \bullet Trim-Lok $^{\textcircled{\scriptsize R}}$ action forces trim to fit snugly against the ceiling
- Socket mounts to trim for optimum performance, and provides consistent vertical lamp position
- Single-lamp vertical 13w (4-pin) G24q-1 or GX24q-1 compact fluorescent

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607




6" Single Vertical Lamp Housing IC & Air Tight

Recessed

Туре _		
P83-AT		

Catalog No.		Dimensions (Inches)	
	Lamping	А В С	
P83-AT	(1) 13w Quad, Triple (GE)	7-7/8 10-3/4 7-1/2	



Specifications:

Wiring

- Universal junction box with snap-out sides
- Removable housing for field inspection of wiring
- Grounding pigtail
- Knockout free Romex clamps
- 1/2" & 3/4" Knock outs for rigid or BX fittings
- Electronic HPF 120/277V ballast

Construction

- Notched housing for chalkline alignment
- Overspray protection
- Full wrap-around plaster frame
- Removable K.O. for remodel use (P8607-01 plaster frame clips also required)
- Galvanized steel construction
- Tooless adjustment for 1/2" to 2-1/2" thick ceilings

Bar Hangers

- Integral nailers for wood joist construction
- Integral T-bar mounting clamps
- Span 24" T-bar spacing
- Lock to secure housing
- Captive
- 90-degree mounting for tight spaces

<u>Labeling</u>

- Complies with Washing State Energy Code (WSEC) requirement for air tight
- UL-CUL listed for damp location and feed-through wiring
- IC rated
- Approved for use in New York City per calendar #42270

Lamp/Trim

- Trim-Lok[®] action forces trim to fit snugly against the ceiling
- Single-lamp vertical 13w (4-pin) G24q-1 compact fluorescent

Rev. 5/08

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607