



Linear Fluorescent

**Strip Lighting**  
**T8 Electronic Ballasts**  
 Energy Star® qualified

Modular Fluorescent

Type \_\_\_\_\_

-30EB

P7265



P7266

P7267

P7268

**Finish**

Catalog No.	Finish		Dimensions (Inches)		
	White	Lamping	A	B	C
P7265	-30EB	1-F17T8	24	3	3-1/8
P7266	-30EB	2-F17T8	24	3	3-1/8
P7267	-30EB	1-F32T8	48	3	3-1/8
P7268	-30EB	2-F32T8	48	3	3-1/8



**Specifications:**

General

- White painted finish
- Steel construction
- Horizontal or vertical mounting, ceiling or wall
- Energy Star® qualified

Mounting

- White post painted cover plate
- 1/2" KO on each end cap for continuous row mounting and on KO on each side near ends
- Mounting KO's near each end on the back plate
- Outlet box covers required if outlet box

is used

Electrical

- 120V, 50/60Hz NPF electronic ballast
- Bi-pin twist and lock sockets on attached flip bracket for ease of installation
- P7265 & P7266 0°F minimum start temp.
- P7267 & P7268 32°F minimum start temp.
- Lamp end-of-life protection, manual reset

Labeling

- UL/CUL listed



Progress Lighting  
 701 Millennium Blvd.  
 Greenville, South Carolina  
 29607

www.progresslighting.com

Rev. 02/14