


PF92341

# Submersible Cast Iron Sump Pump



## Product Features

- 3/10 HP cast iron submersible sump pump with side discharge
- Submersible sump pump for typical residential and commercial applications
- Comes with 10' power cord
- 4.1 amps, 492 watts
- Maximum head of 25 feet
- Cast iron housing and base
- Maximum flow rate of 46 gpm
- Permanent split capacitor motor
- SJE Rhombus vertical float switch
- 1750 RPM
- Liquid temperature range 32° - 120° F
- Discharge size 1-1/2" FNPT
- Handles 3/8" solids
- Stainless steel impeller



Discharge Height	0'	5'	10'	15'	20'	25'
Gallons per Minute	46	36	30	25	12	1
Gallons per Hour	2760	2160	1800	1500	720	60

## Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO pump carries a 5-year limited warranty. In an effort to continually improve our products, we will make design changes from time to time. We reserve the right to ship newly designed products to fill any order unless we agree in writing to do otherwise.

**CALIFORNIA PROP 65 WARNING:** This product may contain chemicals known to the State of California to cause cancer, birth defects or other reproductive harm.  
**Wash Hands After Handling.**

