

W6424

Product: Washing Machine
Mode of installation: Stacked or side by side
Capacity: 2.12 cu.ft.
Spin speed: 1200 rpm
Number of programs: 10 programs

Programs

Auto
Normal white/color
Quick white/color
Super quick
Easy care/sportswear
Synthetics
Wool/hand
Rinse
Spin & drain

Options

1-24 hours
Spin speed: 1200 rpm
Temperature setting

Construction

Quattro™ Suspension – less vibration
SmartSeal™ - no rubber bellows a more
Stainless steel inner/outer drum
Yes

Comfort & safety

Remaining time indicator
Unbalance detection
Water overflow protection
Waterproof bottom plate
Maximized water inlet time
Anti block drain pump
PEX inlet hose
Compartment for liquid detergent
Child lock, detergent compartment



Dimensions and installation

Height: 33 1/2 (851 mm)
Width: 23 1/2 (597 mm)
Depth: 23 7/8 (606 mm)
Length inlet hose: 59 1/16 (1500 mm)
Length outlet hose: 63 (1600 mm)
Weight net: 168 lbs
Weight gross: 172 lbs

Technical information

Connection rating: 2200 W
Current: 10 A
Drum volume: 59 l
Display type: LCD display

Consumption

Noise level washing: 54 dB(A)re 1 pW
Noise level spinning: 73 dB(A)re 1 pW