# **Pipe Hangers**

### B3198H - Hinged Extension Split Pipe Clamp (TOLCO Fig. 302)


Size Range: 3/8" (10mm) to 3" (80mm) pipe


Material: Malleable Iron

**Function:** Designed for suspending non-insulated pipe horizontally or vertically. **Approvals:** Conforms to Federal Specification WW-H-171E & A-A-1192A, Type 25 and Manufacturers Standardization Society ANSI/MSS SP-69 & SP-58, Type 12.

Standard Finish: Plain or Electro-Galvanized

Order By: Part number and finish.







## **B3198R - Extension Split Pipe Clamp**

Size Range: 3/8" (10mm) to 4" (100mm) pipe

Material: Malleable Iron

**Function:** Designed for suspending non-insulated pipe horizontally or vertically. **Approvals:** Conforms to Federal Specification WW-H-171E & A-A-1192A, Type 25 and Manufacturers Standardization Society ANSI/MSS SP-69 & SP-58, Type 12. **Standard Finish:** Plain or Electro-Galvanized. Contact B-Line for alternative finishes

and materials.

Order By: Part number and finish.

C	(Thread Size) Hanger Rod Not Included
/	

Part No. Rod Thread	Pipe Size in. (mm)		Rod Thread Size A	C in. (mm)		Design Load Lbs. (kN)		Approx. Wt./100 Lbs. (kg)	
B3198R- <sup>3</sup> /8	3/8"	(10)	<sup>3</sup> /8"-16	31/32"	(24.6)	180	(.80)	12	(5.4)
B3198R- <sup>1</sup> / <sub>2</sub>	1/2"	(15)	<sup>3</sup> /8"-16	1 <sup>1</sup> /16"	(27.0)	180	(.80)	16	(7.2)
B3198R- <sup>3</sup> /4	3/4"	(20)	<sup>3</sup> /8"-16	1 <sup>7</sup> /32"	(30.9)	180	(.80)	18	(8.1)
B3198R-1	1"	(25)	<sup>3</sup> /8"-16	1 <sup>11</sup> /32"	(34.1)	180	(.80)	24	(10.9)
B3198R-1 <sup>1</sup> /4	1 <sup>1</sup> /4"	(32)	<sup>3</sup> /8"-16	1 <sup>19</sup> /32"	(39.7)	180	(.80)	29	(13.1)
B3198R-1 <sup>1</sup> /2	1 <sup>1</sup> /2"	(40)	<sup>3</sup> /8"-16	1 <sup>23</sup> /32"	(43.6)	180	(.80)	32	(14.5)
B3198R-2	2"	(50)	<sup>3</sup> /8"-16	2"	(50.8)	180	(.80)	39	(17.7)
B3198R-2 <sup>1</sup> /2	21/2"	(65)	1/2"-13	211/32"	(59.5)	300	(1.33)	115	(52.1)
B3198R-3	3"	(80)	<sup>1</sup> /2"-13	2 <sup>23</sup> /32"	(69.0)	300	(1.33)	140	(63.5)
B3198R-4	4"	(100)	<sup>1</sup> /2"-13	3 <sup>11</sup> /32"	(84.9)	300	(1.33)	160	(72.6)





#### **B3198HCT - Hinged Extension Split Pipe Clamp (TOLCO Fig. 301CT)**

Size Range: 1/2" (15mm) to 2" (50mm) copper tubing

Material: Malleable Iron

Function: A rigid support to suspend tubing


horizontally or vertically.

**Approvals:** Conforms to Federal Specification WW-H-171E & A-A-1192A, Type 25 and Manufacturers Standardization Society ANSI/MSS SP-69 & SP-58,

Type 12.

Standard Finish: DURA-COPPER™ Order By: Part number and finish.





	Tubin	g Size	Rod Size	C		Design Load		Approx. Wt./100	
Part No.	in.	(mm)	A	in.	(mm)	Lbs.	(kN)	Lbs.	(kg)
B3198HCT-1/2	1/2"	(15)	<sup>3</sup> /8"-16	5/8"	(15.9)	180	(.80)	8	(3.6)
B3198HCT-3/4	3/4"	(20)	3/8"-16	13/16"	(20.6)	180	(.80)	10	(4.5)
B3198HCT-1	1"	(25)	3/8"-16	<sup>15</sup> /16"	(23.8)	180	(.80)	10	(4.5)
B3198HCT-1 <sup>1</sup> / <sub>4</sub>	1 <sup>1</sup> /4"	(32)	<sup>3</sup> /8"-16	11/8"	(28.6)	180	(.80)	14	(6.3)
B3198HCT-1 <sup>1</sup> / <sub>2</sub>	1 <sup>1</sup> /2"	(40)	<sup>3</sup> /8"-16	1 <sup>9</sup> /16"	(39.7)	180	(.80)	18	(8.1)
B3198HCT-2	2"	(50)	<sup>3</sup> /8"-16	17/8"	(47.6)	180	(.80)	23	(10.4)

## **B3198RCT - Extension Split Pipe Clamp**

Size Range: 1/2" (15mm) to 2" (50mm) copper tubing

Material: Malleable Iron

Function: A rigid support to suspend tubing horizontally or


vertically.

**Approvals:** Conforms to Federal Specification WW-H-171E & A-A-1192A, Type 25 and Manufacturers Standardization

Society ANSI/MSS SP-69 & SP-58, Type 12.

Standard Finish: DURA-COPPER™ Order By: Part number and finish.





	Tubing Size		Rod Size	С		Design Load		Approx. Wt./100	
Part No.	in.	(mm)	A	in.	(mm)	Lbs.	(kN)	Lbs.	(kg)
B3198RCT-3/8	3/8"	(10)	<sup>3</sup> /8"-16	11/16"	(17.5)	180	(.80)	12	(5.4)
B3198RCT-1/2	1/2"	(15)	<sup>3</sup> /8"-16	1 <sup>11</sup> /16"	(17.5)	180	(.80)	12	(5.4)
B3198RCT-3/4	3/4"	(20)	<sup>3</sup> /8"-16	7/8"	(22.2)	180	(.80)	14	(6.3)
B3198RCT-1	1"	(25)	<sup>3</sup> /8"-16	1 <sup>1</sup> /16"	(27.0)	180	(.80)	17	(7.7)
B3198RCT-1 <sup>1</sup> / <sub>4</sub>	1 <sup>1</sup> /4"	(32)	<sup>3</sup> /8"-16	1 <sup>1</sup> /8"	(28.6)	180	(.80)	17	(7.7)
B3198RCT-1 <sup>1</sup> / <sub>2</sub>	11/2"	(40)	<sup>3</sup> /8"-16	1 <sup>5</sup> /16"	(33.3)	180	(.80)	22	(10.0)
B3198RCT-2	2"	(50)	<sup>3</sup> /8"-16	1 <sup>1</sup> /2"	(38.1)	180	(.80)	26	(11.8)

