PF102DC



Washing Machine Valves

Product Features

- Bronze body
- 125 psi
- Operating temperature: 40-160°F
- 3/4" Male hose thread outlet

Available Parts

PF102DC


1/2 FIP WM VLV SATIN



PF102DC

Product Specifications

No.	Part Name	Material	QTY
1	Screw	Stainless	1
2	Handle	Zinc	1
3	Nut	Brass	1
4	Packing	NBR	1
5	Bonnet	Brass	1
6	Washer	Vulcanized	1
7	Stem	Brass	1
8	Seat	NBR	1
9	Screw	Stainless	1
10	Body	Bronze	1



Warranty and Codes

This PROFLO product carries a 1-year limited warranty.

WARNING: This product contains lead or lead compounds known to the State of California to cause cancer and birth defects and other reproductive harm. **Do not use in connection with drinking water. Wash hands after handling.**

