GTW460ASJ

GE Appliances 4.2 DOE Cu. Ft. Capacity Stainless Steel Basket Washer

DIMENSIONS AND INSTALLATION INFORMATION (IN INCHES)

CIRCUIT REQUIREMENTS: An individual, properly-grounded branch circuit, with a three-prong grounding-type receptacle, protected by a 15 or 20 amp circuit breaker or a time-delay fuse, is required.

ELECTRICAL RATING:

120V, 60Hz, 10A

WASHER NOTE:

Washer wall outlet must be located within 36" of service cord entry. Wall outlet must not be located behind dryer.

INSTALLATION INFORMATION:

Before installing, consult installation instructions packed with your washer.







For answers to your Monogram, GE Café[™] Series, GE Profile[™] Series or GE Appliances product questions, visit our website at geappliances.com or call GE Answer Center[®] Service, 800.626.2000.

GTW460ASJ

GE Appliances 4.2 DOE Cu. Ft. Capacity Stainless Steel Basket Washer

FEATURES AND BENEFITS

Deep Fill – Customize your water-fill levels with just the touch of a button. Add a little extra or fill the tub to wash the way you want

Dual-action agitator – Gentle reversing wash action adjusts to the needs of specific clothing types, so clothes always look and feel great

Precise Fill with option of 4 water level selections – Will Automatically measure the load size and add just the right amount of water

Auto Soak – Loosens stains by soaking up to 2 hours

Deep Rinse – When selected, the deep rinse cycle ensure clothes are rinsed of soap residue and fabric softener

Speed Wash – Provides a quick wash for lightly soiled items that are needed in a hurry

Rotary electronic controls with cycle status lights – Know the progress of the wash cycle with just a quick glance

 $700 \mathrm{RPM}$ spin speed – Fast spin speeds remove water efficiently and minimize dry time

Model GTW460ASJWW - White



MODIFIED ENERGY FACTOR (IMEF)	1.35
WATER FACTOR (IWF)	7.0



Specification Revised 1/16