

# GTW485ASJ


## GE® Series 4.2 DOE Cu. Ft. Stainless Steel Capacity Washer

### DIMENSIONS AND INSTALLATION INFORMATION (IN INCHES)

**CIRCUIT REQUIREMENTS:** An individual, properly-grounded branch circuit, with a three-prong grounding-type receptacle, protected by a 15 or 20 amp circuit breaker or a time-delay fuse, is required. Electrical Rating: 120V, 60Hz, 10A

**NOTE:** Washer wall outlet must be located within 36" of service code entry. Wall outlet must not be located behind dryer.

**INSTALLATION INFORMATION:** Before installing, consult installation instructions packed with product for current dimensional data.



**GE APPLIANCES**

For answers to your Monogram, GE Profile™ Series or GE® Series appliance questions, visit our website at [geappliances.com](http://geappliances.com) or call GE Answer Center® service, 800.626.2000.



Listed by  
Underwriters  
Laboratories

Specification Created 7/15

# GTW485ASJ

## GE® Series 4.2 DOE Cu. Ft. Stainless Steel Capacity Washer

### FEATURES AND BENEFITS

ENERGY STAR® certified – Meets or exceeds federal guidelines for energy efficiency for year-round energy and money savings

Deep Fill – Customize your water-fill levels with just the touch of a button. Add a little extra or fill the tub to wash the way you want.

Dual-Action Agitator – Provides gentle, dual-wash action


Deep Rinse – Removes any leftover soap residue

Auto Soak – Loosens stains by soaking up to 2 hours

Speed Wash – Delivers ready-to-go results within minutes

Stain PreTreat – Assists removing tough stains with preprogrammed settings that modify your cycle to treat the four most common stains

Model GTW485ASJWS – White with silver backsplash



MODIFIED ENERGY FACTOR (IMEF)	2.06
WATER FACTOR (IWF)	4.3

