

Diversey

Alpha-HP®  
Multi-Surface  
Disinfectant  
Cleaner

An all-in-one, multi-purpose disinfectant cleaner based on proprietary AHP® technology for use on most water washable hard, nonporous surfaces.

Effective

- Hospital-grade disinfectant
- Bactericidal and virucidal; non-food contact sanitizer
- Hydrogen peroxide active ingredient breaks down to oxygen and water
- Excellent cleaning performance

Easy-to-Use

- Use as spray and wipe cleaning application
- Use as floor cleaner

Versatile

- For use on hard, inanimate, nonporous surfaces such as floors, walls, porcelain, and plastic surfaces in hospitals, nursing homes, schools, colleges and hotels
- Compatible with microfiber cleaning tools



## Use Directions

### For Use as a One-Step Cleaner/Disinfectant

- Pre-clean heavily soiled areas.
- Apply use solution to hard, nonporous environmental surfaces.
- To disinfect, all surfaces must remain wet for 10 minutes.
- Wipe surfaces and let air dry.

**Note:** Rinsing is not necessary unless floors are to be coated with finish or restorer. When cleaning floors position wet-floor signs around area to be cleaned. Floors will be slippery when wet or contaminated with foreign materials. Promptly clean up spills and foreign materials. Do not use on glassware, utensils, or dishes.

### For Use to Clean and Disinfect Shower Rooms, Locker Rooms and Other Large, Open Areas with Floor Drains

- Pre-clean heavily soiled areas.
- Apply use solution to floors, walls and ceilings making sure not to over spray. To disinfect, all surfaces must remain wet for 10 minutes. Scrub using a deck brush or other coarse material as necessary. Rinse surfaces thoroughly and let air dry.

**Note:** When cleaning floors position wet-floor signs around area to be cleaned. Floors will be slippery when wet or contaminated with foreign materials.

### For Use to Clean and Sanitize Non-Food Contact Surfaces

- Dilute at 1 oz. – 2 oz. of product per gallon of water (1:64 to 1:128).
- Pre-clean heavily soiled hard non-porous surfaces.
- Apply use solution until thoroughly wet.
- Let stand for three (3) minutes.
- Then wipe (and allow to air dry).
- Not for use on food contact surfaces or on food preparation areas.

**Note:** Do not use on glassware, utensils, or dishes.

### For Use as a Cleaner/Degreaser

- Dilute product at 1/2 oz. – 2 oz. of product per gallon of water (1:64 to 1:256).
- Apply to hard, nonporous surfaces.
- Wipe surfaces (and let air dry).

**Note:** Not recommended for use on copper, brass or marble.

## Product Specifications

Description	
Color/Form	Clear colorless liquid
EPA Reg. No.	70627-62
Flash Point	>200° F (>93.4° C)
pH	0.8 (Concentrate) 2.05 (Use Dilution 1:64)
Scent	Citrus
Shelf Life	3 years
Solubility	Complete
Specific Gravity	1.036

## Available Items

Product Code	Description/Package Size	Dilution
5549254	2 x 1.5 L/1.59 Qt. RTD® Units	1:64, 1:128, 1:256
5549271	1 x 5 L /1.32 gallon RTD® Unit	1:64, 1:128, 1:256
5549211	2 x 2.5 L/84.5 oz. J-Fill® Bottles	1:64

## Safety Reminder

Please make sure your employees read and understand the product label and Safety Data Sheet before using this product. The label contains directions for use, and both the label and SDS contain hazard warnings, precautionary statements and first aid procedures. SDSs are available on-line at [www.sealedair.com](http://www.sealedair.com) or by calling 888 352 2249. Improper use or dilution may result in damage to surfaces and may result in health and physical hazards that match those of the concentrate. Please refer to the Diversey HazMat Library, only available through Internet Explorer, <http://naextranet.diversey.com/dot/>, for up to date shipping information.