## PF113FC & PF117DC

# Bent Nose Garden Valves



#### **Product Features**

- Bronze body
- 125 psi
- Operating temperature: 40-160°F
- 3/4" Male hose thread outlet


#### **Model Numbers**

PF113FC 3/4 FIP BENT NOSE GRDN VLV PF117DC 1/2 FIP BENT NOSE GRDN VLV



PF113FC

No.	Part Name	Material	QTY
1	Screw	Stainless	1
2	Handle	Zinc	1
3	Nut	Brass	1
4	Packing	NBR	1
5	Garden Valve	Bronze	1
6	Stem	Brass	1
7	Washer	NBR	1
8	Screw	Stainless	1
9	Washer	Vulcanized	1
10	Nut	Brass	1



### Warranty and Codes

This PROFLO product carries a 1-year limited warranty.

**WARNING:** This product contains lead or lead compounds known to the State of California to cause cancer and birth defects and other reproductive harm. **Do not use in connection with drinking water. Wash hands after handling.** 

