


**IPS FAB LATERAL**

<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure Class (psi)</u>	<u>Feed Stock</u>	<u>Dimensions</u> <u>L x C x J (in)</u>	<u>Weight per Item (lbs)</u>	<u>Part #</u>
<b>2"</b> <b>2.375"</b>	100	DR 11	21 x 4 x 16 7/8	2	PEI11HBYKF
	126	DR 9		3	PEI9HBYKF
<b>3"</b> <b>3.500</b>	100	DR 11	23 x 4 x 18 1/4	4	PEI11HBYMF
	126	DR 9		5	PEI9HBYMF
<b>4"</b> <b>4.50"</b>	63	DR 17	24 3/8 x 4 x 19 1/2	7	PEI17HBYPF
	100	DR 11		8	PEI11HBYPF
	126	DR 9		10	PEI9HBYPF
<b>6"</b> <b>6.625"</b>	63	DR 17	31 3/8 x 6 x 24	19	PEI17HBYUF
	100	DR 11		21	PEI11HBYUF
	126	DR 9		28	PEI9HBYUF
<b>8"</b> <b>8.625"</b>	63	DR 17	36 1/4 x 8 x 26 3/8	40	PEI17HBYXF
	100	DR 11		45	PEI11HBYXF
	126	DR 9		54	PEI9HBYXF
<b>10"</b> <b>10.75"</b>	63	DR 17	41 1/4 x 8 x 31	55	PEI17HBY10F
	100	DR 11		81	PEI11HBY10F
	126	DR 9		97	PEI9HBY10F
<b>12"</b> <b>12.75"</b>	63	DR 17	44 x 8 x 33 3/8	82	PEI17HBY12F
	100	DR 11		122	PEI11HBY12F
	126	DR 9		146	PEI9HBY12F
<b>14"</b> <b>14.00"</b>	63	DR 17	55 x 8 x 43 7/8	111	PEI17HBY114
	126	DR 11		165	PEI11HBY14F
	126	DR 9		197	PEI9HBY14F
<b>16"</b> <b>16.00"</b>	63	DR 17	70 x 10 1/2 x 55 3/4	160	PEI17HBY16F
	100	DR 11		239	PEI11HBY16F
	126	DR 9			PEI9HBY16F
<b>18"</b> <b>18.00"</b>	63	DR 17	71 x 10 1/2 x 57 1/4	215	PEI17HBY18F
	100	DR 11		320	PEI11HBY18F
	126	DR 9			PEI9HBY18F

**IPS FAB LATERAL**



<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure Class (psi)</u>	<u>Feed Stock</u>	<u>Dimensions</u> <u>L x C x J (in)</u>	<u>Weight per Item (lbs)</u>	<u>Part #</u>
<b>20"</b> <b>20.00"</b>	63	DR 17	78 x 12 x 62	325	PEI17HBY20F
	100	DR 11		485	PEI11HBY20F
	126	DR 9			PEI9HBY20F
<b>22"</b> <b>22.000"</b>	63	DR 17	80 x 12 x 63 1/2	411	PEI17HBY22F
	100	DR 11		613	PEI11HBY22F
	126	DR 9			PEI9HBY22F
<b>24"</b> <b>24.00"</b>	63	DR 17	82 x 12 x 65	510	PEI17HBY24F
	100	DR 11		760	PEI11HBY24F
	126	DR 9			PEI9HBY24F