





IPS FAB 2 SEG. 30 ELBOW

PE4710

<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure</u> <u>Class (psi)</u>	<u>Feed</u> <u>Stock</u>	<u>Dimension</u> <u>R x C x B (in)</u>	<u>Weight per</u> <u>Item (lbs)</u>	<u>Part #</u>
2" 2.375"	160	DR 11	6 7/8 x 4 x 4 3/8	1	PEI11HB3KF2
	200	DR 9		1	PEI9HB3KF2
	250	DR 7		1	
3" 3.500"	160	DR 11	7 3/8 x 4 x 4 1/2	1	PEI11HB3MF2
	200	DR 9		2	PEI9HB3MF2
	250	DR 7		2	
4" 4.500"	160	DR 11	7 7/8 x 5 x 5 5/8	2	PEI11HB3PF2
	200	DR 9		3	PEI9HB3PF2
	250	DR 7		3	
6" 6.625"	160	DR 11	12 5/8 x 6 x 6 7/8	6	PEI11HB3UF2
	200	DR 9		7	PEI9HB3UF2
	250	DR 7		8	
8" 8.625"	160	DR 11	13 5/8 x 6 1/2 x 7 5/8	11	PEI11HB3XF2
	200	DR 9		13	PEI9HB3XF2
	250	DR 7		15	PEI7HB3XF2
10" 10.750"	100	DR 17	16 1/2 X 6 1/2 X 8	12	PEI17HB310F2
	160	DR 11		18	PEI11HB310F2
	200	DR 9		22	PEI9HB310F2
	250	DR 7		26	PEI7HB310F2
12" 12.750"	100	DR 17	19 1/8 X 8 X 9 3/4	21	PEI17HB312F2
	160	DR 11		32	PEI11HB312F2
	200	DR 9		38	PEI9HB312F2
	250	DR 7		45	
14" 14.000"	100	DR 17	21 X 8 X 9 7/8	27	
	160	DR 11		40	PEI11HB314F2
	200	DR 9		48	PEI9HB314F2
	250	DR 7		58	
16" 16.000"	100	DR 17	24 X 8 X 10 1/8	37	
	160	DR 11		55	PEI11HB316F2
	200	DR 9		66	PEI9HB316F2
	250	DR 7		79	
18" 18.000"	100	DR 17	27 X 8 X 10 1/2	47	PEI17HB318F2
	160	DR 11		70	PEI11HB318F2
	200	DR 9		83	PEI9HB318F2
	250	DR 7		100	
20" 20.000"	100	DR 17	30 X 8 X 10 3/4	60	PEI17HB320F2
	160	DR 11		90	PEI11HB320F2
	200	DR 9		108	PEI9HB320F2
	250	DR 7		129	



IPS FAB 2 SEG. 30 ELBOW

PE4710

<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure</u> <u>Class (psi)</u>	<u>Feed</u> <u>Stock</u>	<u>Dimension</u> <u>R x C x B (in)</u>	<u>Weight per</u> <u>Item (lbs)</u>	<u>Part #</u>
22" 22.000"	100	DR 17	33 X 8 X 11	76	
	160	DR 11		114	
	200	DR 9		136	
	250	DR 7		162	
24" 24.000"	100	DR 17	36 X 8 X 11 1/4	94	PEI17HB324F2
	160	DR 11		141	PEI11HB324F2
	200	DR 9		168	PEI9HB324F2
	250	DR 7		201	
28" 28.000"	100	DR 17	42 X 14 X 17 3/4	198	
	160	DR 11		295	
	200	DR 9		353	PEI9HB328F2
30"	100	DR 17	45 X 14 X 18	228	PEI17HB330F2
	160	DR 11		339	PEI11HB330F2
	200	DR 9		405	
32" 32.000"	100	DR 17	48 X 14 X 18 1/4	266	
	160	DR 11		396	
34" 34.000"	100	DR 17	51 X 14 X 18 1/2	307	
	160	DR 11		458	PEI11HB334F2
36" 36.000"	100	DR 17	54 X 14 X 18 7/8	353	PEI17HB336F2
	160	DR 11		525	PEI11HB336F2
42" 42.000"	80	DR 21	63 X 21 X 26 5/8	513	
	100	DR 17		659	
48" 48.000"	80	DR 21	72 X 21 X 27 1/2	742	
	100	DR 17		900	
54" 54.000"	65	DR 26	81 X 21 X 28 1/2	775	
	80	DR 21		969	