


**IPS FAB 2 SEG. 22.5 ELBOW**  
PE4710

<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure</u> <u>Class (psi)</u>	<u>Feed</u> <u>Stock</u>	<u>Dimension</u> <u>R x C x B (in)</u>	<u>Weight per</u> <u>Item (lbs)</u>	<u>Part #</u>
2" 2.3750"	100	DR 17	13 1/8 x 4 x 4 1/4	1	PEI17HB225KF2
	160	DR 11		1	PEI11HB225KF2
	200	DR 9		1	PEI9HB225KF2
	250	DR 7		1	PEI7HB225KF2
3" 3.50"	100	DR 17	13 5/8 x 4 x 4 3/8	1	PEI17HB225MF2
	160	DR 11		1	PEI11HB225MF2
	200	DR 9		1	PEI9HB225MF2
	250	DR 7		2	PEI7HB225MF2
4" 4.5000"	100	DR 17	14 1/4 x 5 x 5 1/2	2	PEI17HB225PF2
	160	DR 11		2	PEI11HB225PF2
	200	DR 9		3	PEI9HB225PF2
	250	DR 7		3	PEI7HB225PF2
6" 6.625"	100	DR 17	15 1/4 x 6 x 16 5/8	6	PEI17HB225UF2
	160	DR 11		6	PEI11HB225UF2
	200	DR 9		7	PEI9HB225UF2
	250	DR 7		8	PEI7HB225UF2
8" 8.625"	100	DR 17	16 1/4 x 6 1/2 x 7  3/8	10	PEI17HB225XF2
	160	DR 11		10	PEI11HB225XF2
	200	DR 9		12	PEI9HB225XF2
	250	DR 7		15	PEI7HB225XF2
10" 10.750"	100	DR 17	17 1/4 x 6 1/2 x 7  5/8	11	PEI17HB22510F2
	160	DR 11		17	PEI11HB22510F2
	200	DR 9		20	PEI9HB22510F2
	250	DR 7		24	PEI7HB22510F2
12" 12.750"	100	DR 17	19 1/2 x 8 x 9 1/4	19	PEI17HB22512F2
	160	DR 11		28	PEI11HB22512F2
	200	DR 9		34	PEI9HB22512F2
	250	DR 7		42	PEI7HB22512F2
14" 14.000"	100	DR 17	21 x 8 x 9 3/8	23	PEI17HB22514F2
	160	DR 11		35	PEI11HB22514F2
	200	DR 9		41	PEI9HB22514F2
	250	DR 7		51	PEI7HB22514F2
16" 16.000"	100	DR 17	24 x 8 x 9 5/8	31	PEI17HB22516F2
	160	DR 11		46	PEI11HB22516F2
	200	DR 9		55	PEI9HB22516F2
	250	DR 7		66	PEI7HB22516F2
18" 18.000"	100	DR 17	27 x 8 x 9 3/4	41	PEI17HB22518F2
	160	DR 11		60	PEI11HB22518F2
	200	DR 9		71	PEI9HB22518F2
	250	DR 7		85	



**IPS FAB 2 SEG. 22.5 ELBOW**  
PE4710

<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure</u> <u>Class (psi)</u>	<u>Feed</u> <u>Stock</u>	<u>Dimension</u> <u>R x C x B (in)</u>	<u>Weight per</u> <u>Item (lbs)</u>	<u>Part #</u>
20" 20.000"	100	DR 17	30 x 8 x 10	51	PEI17HB22520F2
	160	DR 11		75	PEI11HB22520F2
	200	DR 9		90	PEI9HB22520F2
	250	DR 7		108	PEI7HB22520F2
22" 22.000"	100	DR 17	33 x 8 x 10 1/4	63	
	160	DR 11		93	PEI11HB22522F2
	200	DR 9		111	PEI9HB22522F2
	250	DR 7		133	
24" 24.000"	100	DR 17	36 x 8 x 10 3/8	76	PEI17HB22524F2
	160	DR 11		113	PEI11HB22524F2
	200	DR 9		135	PEI9HB22524F2
	250	DR 7		161	PEI7HB22524F2
26" 26.000"	100	DR 17	39 x 14 x 16 5/8	142	PEI17HB22526F2
	160	DR 11		220	PEI11HB22526F2
	200	DR 9		253	
28" 28.000"	100	DR 17	42 x 14 x 16 3/4	167	PEI17HB22528F2
	160	DR 11		249	PEI11HB22528F2
	200	DR 9		297	PEI9HB22528F2
30" 30.000"	100	DR 17	45 x 14 x 17	194	PEI17HB22530F2
	160	DR 11		289	PEI11HB22530F2
	200	DR9		345	PEI9HB22530F2
32" 32.000"	100	DR 17	48 Xx14 x 17 1/8	223	PEI17HB22532F2
	160	DR 11		333	PEI11HB22532F2
34" 34.000"	100	DR 17	51 x 14 x 17 3/8	255	PEI17HB22534F2
	160	DR 11		380	PEI11HB22534F2
36" 36.000"	100	DR 17	54 x 14 x 17 5/8	286	PEI17HB22536F2
	160	DR 11		426	PEI11HB22536F2
42" 42.000"	80	DR 21	63 x 21 x 25 1/8	462	PEI21HB22542F2
	100	DR 17		563	PEI17HB22542F2
48" 48.000"	80	DR 21	72 x 21 x 25 3/4	617	PEI21HB22548F2
	100	DR 17		753	PEI17HB22548F2
54" 54.000"	65	DR 26	81 x 21 x 26 3/8	652	PEI26HB22554F2
	80	DR 21		799	PEI21HB22554F2