



DIPS FAB 3 SEG. 90 ELBOW

PE4710

<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure Class (psi)</u>	<u>Feed Stock</u>	<u>Dimension</u> <u>R x C x B (in)</u>	<u>Weight per Item (lbs)</u>	<u>Part #</u>
4" 4.80"	160	DR 11	6 X 5 1/2 X 10	6	PED11HB9PF3
	200	DR 9		7	PED9HB9PF3
	250	DR 7		7	PED7HB9PF3
6" 6.90	160	DR 11	9 1/2 X 6 X 13	13	PED11HB9UF3
	200	DR 9		16	PED9HB9UF3
	250	DR 7		16	PED7HB9UF3
8" 9.05"	160	DR 11	10 1/2 X 6 1/2 X 14 1/2	24	PED11HB9XF3
	200	DR 9		29	PED9HB9XF3
	250	DR 7		29	PED7HB9XF3
10" 11.100"	100	DR 17	12 3/4 x 6 1/2 x 18 1/4	26	PED17HB910F3
	160	DR 11		39	PED11HB910F3
	200	DR 9		47	PED9HB910F3
	250	DR 7		54	PED7HB910F3
12" 13.200"	100	DR 17	13 7/8 x 8 1/2 x 19 3/8	43	PED17HB912F3
	160	DR 11		64	PED11HB912F3
	200	DR 9		77	PED9HB912F3
	250	DR 7		82	
14" 15.300"	100	DR 17	14 7/8 x 8 1/2 x 20 3/8	54	PED17HB914F3
	160	DR 11		81	PED11HB914F3
	200	DR 9		97	PED9HB914F3
	250	DR 7		118	PED7HB914F3
16" 17.400"	100	DR 17	16 x 8 1/2 x 23	86	
	160	DR 11		128	PED11HB916F3
	200	DR 9		152	PED9HB916F3
	250	DR 7		169	
18" 19.500"	100	DR 17	17 x 8 1/2 x 24	117	PED17HB918F3
	160	DR 11		174	PED11HB918F3
	200	DR 9		207	PED9HB918F3
	250	DR 7		223	
20" 21.600"	100	DR 17	22 7/8 x 8 1/2 x 27 7/8	162	PED17HB920F3
	160	DR 11		241	PED11HB920F3
	200	DR 9		287	PED9HB920F3
	250	DR 7		312	
24" 25.800"	100	DR 17	25 x 8 1/2 x 30	262	PED17HB924F3
	160	DR 11		321	PED11HB924F3
	200	DR 9		383	PED9HB924F3
	250	DR 7		473	PED7HB924F3