


IPS FAB 3 SEG. 45 ELBOW

PE4710


<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure</u> <u>Class (psi)</u>	<u>Feed</u> <u>Stock</u>	<u>Dimension</u> <u>R x C x B (in)</u>	<u>Weight per</u> <u>Item (lbs)</u>	<u>Part #</u>
2" 2.375"	160	DR 11	13 1/8 x 4 x 7	1	PEI11HB4KF3
	200	DR 9		1	PEI9HB4KF3
	250	DR 7		1	
3" 3.500"	160	DR 11	13 5/8 x 4 x 7 1/4	2	PEI11HB4MF3
	200	DR 9		2	PEI9HB4MF3
	250	DR 7		3	PEI7HB4MF3
4" 4.500"	160	DR 11	14 1/4 x 5 x 8 1/2	3	PEI11HB4PF3
	200	DR 9		4	PEI9HB4PF3
	250	DR 7		5	
6" 6.625"	160	DR 11	15 1/4 x 6 x 10	8	PEI11HB4UF3
	200	DR 9		10	PEI9HB4UF3
	250	DR 7		12	PEI7HB4UF3
8" 8.625"	160	DR 11	16 1/4 x 6 1/2 x 10 7/8	15	PEI11HB4XF3
	200	DR 9		18	PEI9HB4XF3
	250	DR 7		22	PEI7HB4XF3
10" 10.750"	100	DR 17	17 1/4 x 6 1/2 x 11 1/4	16	PEI17HB410F3
	160	DR 11		24	PEI11HB410F3
	200	DR 9		29	PEI9HB410F3
	250	DR 7		35	PEI7HB410F3
12" 12.750"	100	DR 17	19 1/2 x 8 x 13 1/2	27	PEI17HB412F3
	160	DR 11		40	PEI11HB412F3
	200	DR 9		48	PEI9HB412F3
	250	DR 7		60	PEI7HB412F3
14" 14.000"	100	DR 17	21 x 8 x 13 7/8	34	PEI17HB414F3
	160	DR 11		50	PEI11HB414F3
	200	DR 9		60	PEI9HB414F3
	250	DR 7		74	PEI7HB414F3
16" 16.000"	100	DR 17	24 x 8 x 14 3/4	46	PEI17HB416F3
	160	DR 11		70	PEI11HB416F3
	200	DR 9		83	PEI9HB416F3
	250	DR 7		99	PEI7HB416F3



IPS FAB 3 SEG. 45 ELBOW

PE4710

<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure Class (psi)</u>	<u>Feed Stock</u>	<u>Dimension R x C x B (in)</u>	<u>Weight per Item (lbs)</u>	<u>Part #</u>
18" 18.000"	100	DR 17	27 x 8 x 15 5/8	62	PEI17HB418F3
	160	DR 11		92	PEI11HB418F3
	200	DR 9		111	PEI9HB418F3
	250	DR 7		132	PEI7HB418F3
20" 20.000"	100	DR 17	30 x 8 x 16 1/2	80	PEI17HB420F3
	160	DR 11		121	PEI11HB420F3
	200	DR 9		144	PEI9HB420F3
	250	DR 7		171	
22" 22.000"	100	DR 17	33 x 8 x 17 1/4	104	PEI17HB422F3
	160	DR 11		153	PEI11HB422F3
	200	DR 9		183	
	250	DR 7		219	
24" 24.000"	100	DR 17	36 x 8 x 18 1/8	129	PEI17HB424F3
	160	DR 11		191	PEI11HB424F3
	200	DR 9		228	PEI9HB424F3
	250	DR 7		272	PEI7HB424F3
26" 26.000"	100	DR 17	39 x 14 x 25	209	PEI17HB426F3
	160	DR 11		323	PEI11HB426F3
	200	DR 9		371	PEI9HB426F3
	254	DR 7		443	
28" 28.000"	100	DR 17	42 x 14 x 25 7/8	250	PEI17HB428F3
	160	DR 11		372	PEI11HB428F3
	200	DR 9		444	
30" 30.000"	100	DR 17	45 x 14 x 26 5/8	296	PEI17HB430F3
	160	DR 11		441	PEI11HB430F3
	200	DR 9		526	PEI9HB430F3
32" 32.000"	100	DR 17	48 x 14 x 27 1/2	347	
	160	DR 11		516	PEI11HB432F3



IPS FAB 3 SEG. 45 ELBOW

PE4710

<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure</u> <u>Class (psi)</u>	<u>Feed</u> <u>Stock</u>	<u>Dimension</u> <u>R x C x B (in)</u>	<u>Weight per</u> <u>Item (lbs)</u>	<u>Part #</u>
34" 34.000"	100	DR 17	51 x 14 x 28 3/8	404	PE117HB434F3
	160	DR 11		601	PEI11HB434F3
36" 36.000"	100	DR 17	54 x 14 x 29 1/4	466	PEI17HB436F3
	160	DR 11		693	PEI11HB436F3
42" 42.000"	80	DR 21	63 x 21 x 38 3/4	691	
	100	DR 17		844	PEI17HB442F3
48" 48.000"	80	DR 21	72 x 21 x 41 1/4	960	PEI21HB448F3
	100	DR 17		1171	PEI17HB448F3
54" 54.00 "	65	DR 26	81 x 21 x 43 3/4	1051	
	80	DR 21		1287	PEI21HB454F3