


IPS FAB CROSS

PE4710

<u>Nominal Size</u>	<u>Pressure class (psi)</u>	<u>Feed Stock</u>	<u>Dimensions A x C (in)</u>	<u>Weight per Item (lbs)</u>	<u>Part #</u>
2"	160	DR 11	3 15/16 x 10 1/4	3	PEI11HBCKF
3"	160	DR 11	4 x 11 7/16	4	PEI11HBCMF
4"	160	DR 11	4 1/2 x 13 1/2	4	PEI11HBCPF
	200	DR 9		6	PEI9HBXPF
6"	160	DR 11	5 x 16 5/8	12	PEI11HBCUF
	200	DR 9		17	PEI9HBXUF
8"	160	DR 11	7 3/4 x 24 3/16	29	PEI11HBCXF
	200	DR 9		42	PEI9HBCXF
10"	100	DR 17	6 1/2 x 23 3/4	31	PEI17HBC10F
	160	DR 11		42	PEI11HBC10F
	200	DR 9		62	PEI9HBC10F
12"	100	DR 17	8 x 27 3/4	50	PEI17HBC12F
	160	DR 11		69	PEI11HBC12F
	200	DR 9		98	PEI9HBC12F
14"	100	D 17	8 x 30	62	PEI17HBC14F
	160	DR 11		85	PEI11HBC14F
	200	DR 9		121	
16"	100	DR 17	8 x 32	85	PEI17HBC16F
	160	DR 11		116	PEI11HBC16F
	200	DR 9		166	
18"	100	DR17	14 x 46	165	PEI17HBC18F
	160	DR 11		226	PEI11HBC18F
	200	DR 9		322	PEI9HBC18F
20"	100	DR 17	14 x 48	210	PEI17HBC20F
	160	DR 11		288	PEI11HBC20F
	200	DR 9		409	PEI9HBC20F



IPS FAB CROSS

PE4710

<u>Nominal Size</u>	<u>Pressure class (psi)</u>	<u>Feed Stock</u>	<u>Dimensions A x C (in)</u>	<u>Weight per Item (lbs)</u>	<u>Part #</u>
22"	100	DR 17	14 x 50	287	
	160	DR 11		393	
	200	DR 9		559	
24"	100	DR 17	14 x 52	316	
	160	DR 11		433	PEI11HBC24F
	200	DR 9		620	
28"	100	DR 17	14 x 56	316	
	160	DR 11		433	
	200	DR 9		620	
30"	100	DR 17	14 x 58	316	
	160	DR 11		433	
32"	100	DR 17	14 x 60	316	
	160	DR 11		433	
36"	100	DR 17	20 X 76	316	PEI17HBC36F
	160	DR 11		433	