


# WOLSELEY

INDUSTRIAL GROUP


## IPS FLANGE ADAPTER



PE4710

<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure Class (psi)</u>	<u>SDR</u>	<u>Dimensions</u> <u>AxTxC(in)</u>		<u>Weight Per Item(lbs)</u>	<u>Part #</u>
IPS <b>3/4"</b> 1.050"	200	DR 11	4.00 X 0.39 X 1.85		0.10	PEI11ABFF
	250	DR 9			0.10	PEI9ABFF
	335	DR 7			0.10	PEI7ABFF
IPS <b>1"</b> 1.315"	200	DR 11	4.00 X 0.39 X 2.36		0.20	PEI11ABFG
	250	DR 9			0.20	PEI9ABFG
	335	DR 7			0.20	PEI7ABFG
IPS <b>1-1/4"</b> 1.660"	200	DR 11	4.00 X 0.39 X 2.80		0.30	PEI11ABFH
	250	DR 9			0.30	PEI9ABFH
	335	DR 7			0.30	PEI7ABFH
IPS <b>1-1/2"</b> 1.660"	200	DR 11	4.00 X .39 X 3.15		0.35	PEI11ABFJ
	250	DR 9			0.35	PEI9ABFJ
	335	DR 7			0.40	PEI7ABFJ
IPS <b>2"</b> 2.375	200	DR 11	5.98 X 0.40 X 4.00		0.33	PEI11ABFK
	250	DR 9			0.40	PEI9ABFK
	335	DR 7			0.47	PEI7ABFK
IPS <b>*2-1/2"</b> 2.875"	200	DR 11	6.00 X .60 X 5.00		0.75	PEI11ABFL
	250	DR 9			0.75	
	335	DR 7			0.80	
IPS <b>3"</b> 3.50"	125	DR 17	5.98 X .598 X 5.00		0.83	PEI17ABFM
	200	DR 11			0.83	PEI11ABFM
	250	DR 9	5.98 X .625 X 5.00		1.20	PEI9ABFM
		DR 7			1.25	PEI7ABFM
IPS <b>4"</b> 4.50"	125	DR 17	6.00 X .80 X 6.60		1.70	PEI17ABFP
	200	DR 11			1.70	PEI11ABFP
	250	DR 9	6.00 X 1.00 X 6.00		2.10	PEI9ABFP
		DR 7			2.30	PEI7ABFP
IPS <b>5"</b> 5.563"	125	DR 17	8.00 X .64 X 7.50		2.50	
	200	DR 11			2.50	PEI11ABFS
	250	DR 9	8.00 X .98 X 7.50		2.50	
IPS <b>6"</b> 6.625	125	DR 17	7.99 X .80 X 8.50		5	PEI17ABFU
	200	DR 11			6	PEI11ABFU
	250	DR 9	8.00 X 1.00 X 8.50		7	PEI9ABFU
		DR 7		8.00 X 1.20 X 8.50		7
IPS <b>8"</b> 8.625	125	DR 17	9.02 X 1.00 X 10.660		6	PEI17ABFX
	200	DR 11			6	PEI11ABFX
	250	DR 9	9.02 X 1.625 X 10.60		7	PEI9ABFX
		DR 7		9.02 X 1.625 X 10.60		11


**IPS FLANGE ADAPTER**



PE4710

<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure Class (psi)</u>	<u>SDR</u>	<u>Dimensions</u> <u>AxTxC(in)</u>	<u>Weight Per Item(lbs)</u>	<u>Part #</u>
<b>IPS 10"</b> 10.75	125	DR 17	11.00 X 1.28 X 12.80	10	PEI17ABF10
	200	DR 11	11.00 X 1.29 X 12.80	10	PEI11ABF10
	250	DR 9	11.00 X 1.50 X 12.80	17	PEI9ABF10
	335	DR 7	11.00 X 2.00 X 12.80	25	PEI7ABF10
<b>IPS 12"</b> 12.75"	125	DR 17	11.00 X 1.54 X 15.25	18	PEI17ABF12
	200	DR 11	11.00 X 1.54 X 15.25	18	PEI11ABF12
	250	DR 9	11.00 X 1.87 X 15.25	26	PEI9ABF12
	335	DR 7	11.00 X 2.30 X 15.25	29	PEI7ABF12
<b>IPS 14"</b> 14.00"	125	DR 17	11.00 X 1.63 X 17.50	28	PEI17ABF14
	200	DR 11	11.00 X 1.70 X 17.50	28	PEI11ABF14
	250	DR 9	11.00 X 2.00 X 17.50	28	PEI9ABF14
	335	DR 7	11.00 X 2.60 X 17.50	41	PEI7ABF14
<b>IPS 16"</b> 16.00"	125	DR 17	12.00 X 1.88 X 20.00	37	PEI17ABF16
	200	DR 11	12.00 X 1.90 X 20.00	37	PEI11ABF16
	250	DR 9	12.00 X 2.25 X 20.00	37	PEI9ABF16
	335	DR 7	12.00 X 3.00 X 20.00	53	PEI7ABF16
<b>IPS 18"</b> 18.00"	125	DR 17	12.00 X 2.00 X 21.10	44	PEI17ABF18
	200	DR 11	12.00 X 2.10 X 21.10	44	PEI11ABF18
	250	DR 9	12.00 X 2.50 X 21.10	44	PEI9ABF18
	335	DR 7	12.00 X 3.86 X 21.10	64	
<b>IPS 20"</b> 20.00"	125	DR 17	12.00 X 2.27 X 23.50	56	PEI17ABF20
	200	DR 11	12.00 X 2.30 X 23.50	56	PEI11ABF20
	250	DR 9	12.00 X 3.49 X 23.50	56	PEI9ABF20
	335	DR 7	12.00 X 3.63 X 23.50	62	PEI7ABF20
<b>IPS 22"</b> 22.00"	125	DR 17	12.00 X 2.50 X 25.60	68	PEI17ABF22
	200	DR 11	12.00 X 2.50 X 25.60	68	PEI11ABF22
	250	DR 9	12.00 X 3.92 X 25.60	68	PEI9ABF22
<b>IPS 24"</b> 24.00"	125	DR 17	14.00 X 2.75 X 27.90	83	PEI17ABF24
	200	DR 11	14.00 X 2.90 X 27.90	83	PEI11ABF24
	250	DR 9	14.00 X 4.36 X 27.90	83	PEI9ABF24
<b>IPS 26"</b> 26.00"	125	DR 17	14.00 X 2.96 X 27.75	87	PEI17ABF26
	200	DR 11	14.00 X 2.96 X 27.75	117	PEI11ABF26
<b>IPS 28"</b> 28.00"	125	DR 17	14.00 X 3.18 X 32.00	90	PEIPS17BFA28
	200	DR 11	14.00 X 3.18 X 32.00	129	PEI11ABF28

**IPS FLANGE ADAPTER**



PE4710

<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure Class (psi)</u>	<u>SDR</u>	<u>Dimensions</u> <u>AxTxC(in)</u>		<u>Weight Per Item(lbs)</u>	<u>Part #</u>
<b>IPS 30"</b> <b>30.00"</b>	125	DR 17	14.00 X 3.41 X 34.00		98	PEI17HBF30
	200	DR 11	14.00 X 3.41 X 34.00		134	PEI11ABF30
<b>IPS 32"</b> <b>32.00"</b>	65	DR 32.5	14.00 X 3.64 X 36.125		95	PEI32ABF32
	125	DR 17			106	PEI17HBF32
<b>IPS 34"</b> <b>34.00"</b>	65	DR 32.5	14.00 X 2.24 X 38.125		120	PEI32ABF34
	125	DR 17	14.00 X 3.86 X 38.125		135	PEI17ABF34
<b>IPS 36"</b> <b>36.00"</b>	65	DR 32.5	14.00 X 2.37 X 38.125		130	PEI32HBF36
	125	DR 17	14.00 X 4.09 X 38.125		141	PEI17HBF36
<b>IPS 42"</b> <b>42.00"</b>	65-100	DR 32.5-21	CALL		152	PEI26HBF42 PEI32HBF42
<b>IPS 48"</b> <b>48.00"</b>	65	DR 32.5	CALL		150	
	80	DR 26			170	
<b>IPS 54"</b> <b>54.00"</b>	65	DR 32.5	CALL		230	PEI26ABF54
	80	DR 26	CALL		250	PEI32ABF54