

# Fairfax® Widespread Bathroom Sink Faucet K-12265-4

### **Features**

- Metal construction.
- Brass valve bodies.
- Quarter-turn washerless ceramic disc valves.
- Pop-up drain with lift rod and tailpiece.
- 5" (127 mm) spout reach.
- For 8" (203 mm) or 16" (406 mm) centers.
- Stationary spout.
- Lower flow aerator options are available. (Please refer to the Kohler Price Book).
- 1.5 gal/min (5.7 l/min) maximum flow rate [max at 60 psi (4.14 bar)].

## **Optional Accessories**

1077792 Fairfax Two-handle Plug Button Set





### Codes/Standards

ASME A112.18.1/CSA B125.1 NSF 61 NSF 372 DOE - Energy Policy Act 1992 EPA WaterSense® ADA ICC/ANSI A117.1 All applicable US Federal and State material regulations

# **KOHLER® Faucet Lifetime Limited Warranty**

See website for detailed warranty information.

## **Available Color/Finishes**


Color tiles intended for reference only.

		•
Color	Code	Description
	CP	Polished Chrome
	РВ	Vibrant® Polished Brass
	G	Brushed Chrome
	BN	Vibrant® Brushed Nickel
	BV	Vibrant® Brushed Bronze
	BX	Vibrant® Brazen Bronze
	СВ	Polished Chrome with Vibrant® Polished Brass Accents





# Fairfax® Widespread Bathroom Sink Faucet K-12265-4



## **Technical Information**

All product dimensions are nominal.

Spout reach: 5" (127 mm)

Drain included: YES
Drain tailpiece YES

included:

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Pressure: 60 psi (4.1 bar)

### **Notes**

Install this product according to the installation guide.

ADA compliant when installed to the specific requirements of these regulations.

