

Coralais® Centerset Bathroom Sink Faucet K-15199-F

Features

- Metal construction.
- One-piece, self-contained ceramic disc valve allows both volume and temperature control.
- Temperature memory allows faucet to be turned on and off at any temperature setting.
- High-temperature limit setting for added safety.
- 4-1/4" (108 mm) spout reach.
- Stationary spout.
- Metal throat plate.
- For 4" (102 mm) centers.
- Flexible connections.
- Less drain.
- 1.5 gal/min (5.7 l/min) maximum flow rate [max at 60 psi (4.14 bar)].

Optional Accessories

1160594 Large Spray Aerator 0.35 gpm (1.3 l/min)



ADA

Codes/Standards


ASME A112.18.1/CSA B125.1 NSF 61 NSF 372 DOE - Energy Policy Act 1992 ADA ICC/ANSI A117.1 All applicable US Federal and State material regulations

KOHLER® One-Year Limited Warranty See website for detailed warranty information.





Coralais® Centerset Bathroom Sink Faucet K-15199-F



Technical Information

All product dimensions are nominal.

Spout reach: 4-1/4" (108 mm)

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Pressure: 60 psi (4.1 bar)

Notes

Install this product according to the installation guide.

ADA compliant when installed to the specific requirements of these regulations.

