


Features

- Brass construction
- One-piece, self-contained ceramic disc valve allows both volume and temperature control
- Temperature memory allows faucet to be turned on and off at any temperature setting
- High-temperature limit setting for added safety
- 2.2 gallons (8.3 L) per minute maximum flow rate
- Lower flow aerator options are available (refer to the Kohler Price Book)
- Single-hole mounting
- Lever handle
- Flexible connections for easy installation
- Includes pop-up drain
- 3-7/16" (87 mm) spout length

BIDET FAUCET K-19481



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.18.1/CSA B125.1

Colors/Finishes

- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Colors/Finishes	
		<input type="checkbox"/> CP	<input type="checkbox"/> Other ____
K-19481	Bidet faucet		


Product Specification

Single-handle bidet faucet shall be of brass construction. Product shall have a one-piece, self-contained ceramic disc valve, allowing volume and temperature control. Product shall feature temperature memory, allowing the faucet to be turned on and off at any temperature setting. Product shall feature a high-temperature limit stop. Product shall feature single-hole mounting. Product shall have a 2.2 gallon (8.3 liter) per minute flow rate and 3-7/16" (87 mm) spout length. Product shall have lower flow aerator options available. Product shall include flexible connections for easy installation, lever handle, and pop-up drain. Faucet shall be Kohler Model K-19481-_____.

SYMBOL™

Installation Notes

Install this product according to the installation guide.



Product Diagram