

## **Margaux**® Widespread Bathroom Sink Faucet

K-16232-4

#### **Features**

- Brass construction.
- Brass valve bodies.
- Pop-up drain with lift rod and tailpiece.
- Lever handles.
- For 8" (203 mm) or 16" (406 mm) centers.
- 5-3/8" (137 mm) spout reach.
- Stationary spout.
- Quarter-turn washerless ceramic disc valves.
- 1.5 gal/min (5.7 l/min) maximum flow rate [max at 60 psi (4.14 bar)].





#### Codes/Standards

ASME A112.18.1/CSA B125.1 **NSF 61 NSF 372** DOE - Energy Policy Act 1992 EPA WaterSense® ADA ICC/ANSI A117.1

All applicable US Federal and State material regulations

### **KOHLER® Faucet Lifetime Limited** Warranty

See website for detailed warranty information.

#### **Available Color/Finishes**


Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	SN	Vibrant® Polished Nickel
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel
	BV	Vibrant® Brushed Bronze





# Margaux® Widespread Bathroom Sink Faucet



#### **Technical Information**

All product dimensions are nominal.

Spout reach: 5-3/8" (137 mm)

Drain included: YES
Drain tailpiece YES

included:

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Pressure: 60 psi (4.1 bar)

#### **Notes**

Install this product according to the installation guide.

ADA compliant when installed to the specific requirements of these regulations.

