# **KOHLER**<sub>®</sub>

#### Features

- Two-piece toilet.
- Elongated bowl offers added room and comfort.
- Left-hand nested trip lever offers a choice of 1.1 or 1.6 gallons per flush (gpf).
- 2-1/8-inch glazed trapway.
- Coordinates with other products in the Wellworth collection.
- Combination consists of the the K-4198 bowl and the K-4458 tank.

#### Technology

 Dual-flush technology allows you to choose between a full- or partial-flush.

#### Installation

- Standard 12-inch rough-in
- Three-bolt installation.

### Water Conservation & Rebates

- WaterSense® toilets meet strict EPA flushing guidelines, including using at least 20 percent less water than 1.6-gallon toilets.
- Eligible for consumer rebates in some municipalities.

**Wellworth**<sup>®</sup>





For complete listing of available colors, go to kohler.com.



Codes/Standards ASME A112.19.2/CSA B45.1 EPA WaterSense®

#### KOHLER<sup>®</sup> One-Year Limited Warranty

See website for detailed warranty information.

## **Product Specification**


Toilet shall be 30" (762 mm) in length, 18" (457 mm) in width, and 29-1/4" (743 mm) in height. Toilet shall be made of vitreous china. Toilet shall be two-piece. Product shall feature 1.6 gpf (6.1 lpf) or 1.1 gpf (4.2 lpf). Toilet shall be left-hand trip lever. Toilet shall be Class Five® dual flushing system. Toilet shall be 12" (305 mm) rough-in. Toilet shall be Kohler Model K-3988.







# Wellworth® Class Five® Dual Flush Toilet K-3988



#### **Technical Information**

All measurements are Toilet style:	approximate only. Two-piece
Bowl shape:	Elongated front
Passageway:	2-1/8" (54 mm)
Flush rate - full:	1.6 gpf (6.1 lpf)
Flush rate - short:	1.1 gpf (4.2 lpf)
Water area:	11-1/4" x 8-1/4" (286 mm x 210 mm)
Water depth from rim:	5-1/4" (133 mm)
Rough-in:	12" (305 mm)
Seat hole centers:	5-1/2" (140 mm)

#### **Installation Notes**

Install this product according to the installation guide.

