



**Underscore®**

5' Whirlpool Bath

**K-1167-H2**



### Features

- End drain.
- Slotted overflow for deep soaking.
- Integral lumbar support.
- 60" (1524 mm) x 30" (762 mm) x 19" (483 mm)

### Material

- Acrylic

### Hydrotherapy

- Eight fully adjustable Flexjet™ hydrotherapy jets for water flow and direction.
- Built-in 1500 W heater.
- Lighted keypad control.

### Installation

- Drop-in or under-mount.

### Required Accessories

- K- 7271 Brass Slotted Overflow Bath Drain
- K- 9698 Flexjet® Whirlpool Trim Kit

or

- K- 7272 PVC Slotted Overflow Bath Drain
- K- 9698 Flexjet® Whirlpool Trim Kit

### Recommended Accessories

- K- 1491 Bath/Whirlpool Pillow
- K- 1601 Bath/Whirlpool Footstop
- K- 1703 Whirlpool Remote Control
- K- 531 Under-mount Installation Kit
- K- 9497 2-1/2" Keypad Trim
- K- 24916 Wireless Music Kit



### Codes/Standards











ASME A112.19.7/CSA B45.10  
CSA B45.5/IAPMO Z124  
ASTM E162  
ASTM E662  
UL 1795  
CSA C22.2 No. 218.2  
Greenguard UL 2818 - Gold

### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

### Available Color/Finishes

*Color tiles intended for reference only.*

| Color  | Code | Description   |
|--|------|---------------|
|  | 0    | White         |
|  | 96   | Biscuit       |
|  | 47   | Almond        |
|  | NY   | Dune          |
|  | 95   | Ice™ Grey     |
|  | G9   | Sandbar       |
|  | 33   | Mexican Sand™ |
|  | K4   | Cashmere      |
|  | 58   | Thunder™ Grey |
|  | 7    | Black Black™  |


USA/Canada: 1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com).

3-27-2016 05:26

THE BOLD LOOK  
OF **KOHLER**®



### Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI) or Residual Current Device (RCD).

Pump: 240 V, 20 A, 50/60 Hz

### Technical Information

All product dimensions are nominal.

|                              |   |
|------------------------------|---|
| Installation:                | Drop-in, Under-mount                          |
| Drain location:              | End   |
| Basin area, bottom:          | 42-3/8" x 20" (1076 mm x 508 mm)              |
| Basin area, top:             | 54-3/8" x 24-5/16" (1381 mm x 618 mm)         |
| Weight:                      | 121 lbs (54.9 kg)                             |
| Minimum floor load:          | 52 lbs/ft² (253.9 kg/m²)                      |
| Water depth:                 | 15-1/16" (383 mm)                             |
| Water capacity:              | 59.8 gal (226.4 L)                            |
| Cutout:                      | Drop-in, 59-1/2" x 28-1/2" (1511 mm x 724 mm) |
| Electrical component rating: | Pump: 240 V, 11 A, 50/60 Hz, 1500 W           |
| Pump speed:                  | Variable                                      |

### Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.