



Features

- Fold-up seat on left side.
- Molded-in floor pattern.
- 36" (914 mm) x 36" (914 mm) x 81-3/8" (2067 mm) inside finished dimensions.



ADA

Codes/Standards

CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
Greenguard UL 2818 - Gold
ADA
ICC/ANSI A117.1

KOHLER® One-Year Limited Warranty


See website for detailed warranty information.




Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

- | | | |
|--|----|---------|
|  | 0 | White |
|  | 96 | Biscuit |
|  | 47 | Almond |

*Recess opening must be 45-1/4" (1149 mm) x 84-1/4" (2140 mm).	
	Represents control area for faucets
	Represents 24" (610 mm) wall mount slide bar.
	Represents clear floor space for 36" (914 mm) x 48" (1219 mm).



Technical Information

All product dimensions are nominal.

Installation: 3-Wall Alcove

Drain location: Center rear

Drain hole diameter: 3-3/8" (86 mm)

Weight: 170 lbs (77.1 kg)

Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

For increased accessibility, utilize "pit" installation as detailed in installation guide.

The fixture is not drilled for supply fittings.

Shimming may be required to level the fixture.

Stud opening tolerance + 1/4" (6 mm).

When fire rated construction is specified, dimensions are to the inside of the fire-rated wall.

Some shimming between stud frame and fixture may be required.

For optimum accessibility, specify faucets and fittings to install and operate within the control area shown.

ADA compliant when installed to the specific requirements of these regulations.