

Features


- Brass construction
- Requires an AC power supply
- Wall-mounting for Touchless™ faucets
- 0.5 gal/min (1.9 l/min) flow rate
- Insight™ adaptive infrared technology

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ICC/ANSI A117.1
- ASME A112.18.1/CSA B125.1
- Energy Policy Act of 1992
- ADA

WALL-MOUNT VALVE **K-11842** ALSO K-11843



Colors/Finishes

• NA: None applicable

Accessories

- CP: Polished Chrome
- NA: None applicable
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description			Co	lors/Finishes	
K-11842	Wall-mount valve, square trim				NA	
K-11843	Wall-mount valve, round trim (shown)				NA	
Required Accessories						
K-13480	AC single supply transformer				□NA	
K-13481	AC multi-output power supply				□ NA	
Optional Accessories						
K-7129-A	Grid drain with overflow		□ CP		☐ Other	
K-7129	Grid drain without overflow		□ CP		☐ Other	
K-13601	Thermostatic mixing valve			□ NA		

Product Specification


The Touchless™ wall-mounting valve shall be made of brass construction. Valve shall have a 0.5 gal/min (1.9 l/min) flow rate. Valve shall feature Insight adaptive infrared technology. Valve shall require an AC power supply. Wall-mount valve shall be Kohler Model K-11842-NA or K-11843-NA.


Installation Notes

Install this product according to the installation guide.

This product requires an AC power supply (not included).

Reference the installation instructions provided with the valve for specific framing information.





^{*}Spout length varies dependant on valve roughing-in depth.

Product Diagram

