



Gilford™
Utility Sink
K-12784

Features

- Vitreous china.
- Wall-mount.
- Rectangular basin.
- Single basin.
- Single faucet hole.
- 24" (610 mm) x 22-1/8" (562 mm) x 8-5/8" (219 mm)

Recommended Accessories

K- 1814-P Wall Mount Sink Brackets

Optional Accessories

K- 9000 P-Trap

K-9115



Codes/Standards

ASME A112.19.2/CSA B45.1

KOHLER® One-Year Limited Warranty


See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
--	---	-------



Technical Information

All product dimensions are nominal.

Bowl configuration: Single

Installation: Wall-mount

Bowl area (Only) Length: 22" (559 mm)
Width: 18" (457 mm)
Water depth: 8-5/8" (219 mm)

Number of deck holes: 1

Faucet hole(s): 1-3/8" (35 mm)

Drain hole: 2-1/4" (57 mm)

Notes

Install this product according to the installation guide.