

# **Devonshire®**

5' Whirlpool Bath K-1357-LA



### **Features**

- Integral flange.
- Left drain.
- Integral lumbar support and armrests for comfort.
- Integral apron with removable access panel.
- Textured bottom surface.
- Coordinates with other products in the Devonshire® collection.
- 60" (1524 mm) x 32" (813 mm) x 20" (508 mm)

### **Material**

Acrylic

## **Hydrotherapy**

- Single-speed whirlpool offers 8 fully adjustable hydro-massage jets for water flow and direction.
- Pump with air switch for whirlpool.

### Installation

Alcove

### **Recommended Accessories**

K- 7161-AF Bath Drain K- 24916 Wireless Music Kit



### Codes/Standards

ASME A112.19.7/CSA B45.10 CSA B45.5/IAPMO Z124 ASTM E162 ASTM E662 UL 1795 CSA C22.2 No. 218.2 Greenguard UL 2818 - Gold

# **KOHLER® One-Year Limited Warranty**

See website for detailed warranty information.

### **Available Color/Finishes**

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Biscuit
	47	Almond
	NY	Dune
	G9	Sandbar








# **Devonshire®**


5' Whirlpool Bath K-1357-LA

No change in measurements if connected with drain illustrated. (K-7161-AF)









### **Required Electrical Service**

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI) or Residual Current Device (RCD).

Pump: 120 V, 15 A, 50/60 Hz

#### **Technical Information**

All product dimensions are nominal.

Installation:

3-Wall Alcove

Drain location: Left

Basin area, bottom: 42" x 20" (1067 mm x 508 mm) Basin area, top: 51" x 24" (1295 mm x 610 mm)

Weight: 135 lbs (61.2 kg)
Minimum floor load: 50 lbs/ft² (244.1 kg/m²)

Water depth: 14" (356 mm)
Water capacity: 60 gal (227.1 L)

Electrical component Pump: 120 V, 7 A, 60 Hz

rating:

Pump speed: Single

#### **Notes**

Measure your actual product for rough-in details. Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Provide one grounded electrical outlet within 24" (610 mm) of each component.

