

Purist® Widespread Bathroom Sink Faucet K-14410-3

Features

- Metal construction.
- Brass valve bodies.
- Cross handles.
- 5" (127 mm) spout reach.
- Pop-up drain with lift rod and tailpiece.
- For 8" (203 mm) or 16" (406 mm) centers.
- Reversible quarter-turn washerless ceramic disc valves.
- Lower flow aerator options are available. (Please refer to the Kohler Price Book).
- 1.5 gal/min (5.7 l/min) maximum flow rate [max at 60 psi (4.14 bar)].





Codes/Standards

ASME A112.18.1/CSA B125.1 NSF 61 NSF 372 DOE - Energy Policy Act 1992 EPA WaterSense® ADA ICC/ANSI A117.1

OBC

All applicable US Federal and State material regulations

KOHLER® Faucet Lifetime Limited Warranty


See website for detailed warranty information.





Purist®

Widespread Bathroom Sink Faucet K-14410-3



Technical Information

All product dimensions are nominal.

Spout reach: 5" (127 mm)

Drain included: YES
Drain tailpiece YES

included:

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Pressure: 60 psi (4.1 bar)

Notes

Install this product according to the installation guide.

ADA, OBC compliant when installed to the specific requirements of these regulations.

