

Features

- Fits minimum 21-inch base cabinet if installed as top-mount.
- Fits minimum 24-inch base cabinet if installed as under-mount.
- Single bowl.
- 12-1/2-inch depth.
- 3 faucet holes (-3).

Material

• KOHLER enameled cast iron.

Installation

Cutout template is included.

Recommended Accessories

K- 9000 P-Trap

Optional Accessories

K- 8801 Sink Strainer



Codes/Standards ASME A112.19.1/CSA B45.2

KOHLER[®] Enameled Cast Iron Kitchen Sink - Lifetime Limited Warranty

See website for detailed warranty information.

Available Color/Finishes


Color tiles intended for reference only.

Color	Code	Description
\bigcirc	0	White
\bigcirc	FF	Sea Salt™
\bigcirc	96	Biscuit
\bigcirc	47	Almond
\bigcirc	FD	Cane Sugar™
\bigcirc	NY	Dune
	95	Ice™ Grey
\bigcirc	G9	Sandbar
\bigcirc	33	Mexican Sand™
	K4	Cashmere
	FT	Basalt
	58	Thunder™ Grey
	20	Suede
	KA	Black 'n Tan
	FP	Caviar
	7	Black Black™



Park Falls[™] Utility Sink K-19022-3





Technical Information

All product dimensions	s are nominal.
Bowl configuration:	Single
Installation:	Top-mount, Under-mount
Bowl area (Only)	Length: 17-1/2" (445 mm) Width: 15-3/16" (386 mm) Bowl depth: 12-1/2" (318 mm) Water depth: 12-1/2" (318 mm)
Number of deck holes:	3
Faucet hole(s):	1-3/8" (35 mm)
Drain hole:	3-7/8" (98 mm)
Template:	Top-mount/Under-mount, 1079985-7, required, included

Notes

Install this product according to the installation guide.

