

# **KOHLER**®

Utility Sink K-19022-2

#### **Features**

- Fits minimum 21-inch base cabinet if installed as top-mount.
- Fits minimum 24-inch base cabinet if installed as under-mount.
- Single bowl.
- 12-1/2-inch depth.
- 2 faucet holes (-2).
- Includes cutout templates.

#### Material

KOHLER enameled cast iron.

#### Installation

Top-mount or Under-mount installation.

#### **Recommended Accessories**

K- 9000 P-Trap

## **Optional Accessories**

K-8801 Sink Strainer



# Codes/Standards

ASME A112.19.1/CSA B45.2

See website for detailed warranty information.

#### Available Color/Finishes


Color tiles intended for reference only.

Color	Code	Description
	0	White
	FF	Sea Salt™
	96	Biscuit
	47	Almond
	FD	Cane Sugar™
	NY	Dune
	95	Ice™ Grey
	G9	Sandbar
	33	Mexican Sand™
	K4	Cashmere
	FT	Basalt
	58	Thunder™ Grey
	20	Suede
	KA	Black 'n Tan
	FP	Caviar
	7	Black Black™





Utility Sink **K-19022-2** 



## **Technical Information**

All product dimensions are nominal.

Bowl configuration: Single

Installation: Top-mount, Under-mount Bowl area (Only) Length: 17-1/2" (445 mm)

Width: 15-3/16" (386 mm) Bowl depth: 12-1/2" (318 mm) Water depth: 12-1/2" (318 mm)

Number of deck holes: 2

Faucet hole(s): 1-3/8" (35 mm)
Drain hole: 3-7/8" (98 mm)

Template: Top-mount/Under-mount, 1079985-7,

required, included

#### **Notes**

Install this product according to the installation guide.

